



Catalog No. THQB1120AF

Description: ARC FAULT CB 1P - BOLT ON

UPC No 783164329711

Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line

Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

Descriptors

Category	Q-Line Miniature Circuit Breakers
GO Schedule	B1

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac, 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Product Line	TEY / Q-Line (Bolt-On)
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR10263

Publications

Title	Publication No.	Publication Type
Q-Line Bolt-On MCCB, 100A Frame 1- Pole with Arc Fault Protection, Drawing 1-Page fully dimensioned outline drawing in .pdf format	10082555-SH3	Drawings-Outline and Dimensional
Ground Fault Circuit Interrupter with Self-Test Feature (GFCI) Rev A. 2 Pages. Installation, troubleshooting, and testing guide for type THQ/THHQ 15A-30A, 1 Pole circuit breakers.	GEH-4338	Installation and Instruction
15A-20A, 1 Pole Installation Instructions	GEH-41543	Installation and Instruction

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.