



Catalog No. SG600J

Description: 600A NEMA 12 C/B ENL NO KO'S

UPC No 783164219616

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: For 3 phase, 4-wire ground fault, order neutral kit and neutral current sensor kit (kits must be mounted in enclosure). Enclosure does not include knockouts (NEMA Type 12).

ACCESSORIES:

Neutral Kit (non-GF applications): TNIA600

Neutral Kit(s) (for GF applications): TNIA600VG

Neutral Current Sensor(s) (for GF applications): TSRG206

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	SG600
Amperage	600 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	208C2886SH1
GSA Compliance	No

Dimensions

Height	44.9 in
Depth	8.4 in
Width	18.0 in
Weight	63.5 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 600 amp max. Product Number SG600J. 1 page outline drawing in .pdf format.	208C2886-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.