



## Catalog No. TH2223M

Description: 100A 2P MD N12 240V FUSIBLE

UPC No 783164092615

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Mill

- Designed specifically for the rugged conditions found in steel mills, cement foundries and other process-related environments.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating - field convertible to compression connectors.
- Full cover interlocks.

### Descriptors

Category	Mill
GO Schedule	SB

### Specifications

Voltage	240 AC
Amperage	100 A
Poles	2
Wires	2
Fusing	Fusible
Enclosure	NEMA 12 Drip/Dust-tight
Options	None
Wire Range (Cu/Al)	14-1/0 CU;12-1/0 AL
240 Vac, NEC Std, 1-ph	7.5 hp
240 Vac, Time Delay, 1-ph	15.0 hp
250 Vdc	10.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	23.4 in
Depth	5.0 in
Width	13.4 in
Weight	24.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">200A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH128	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.