



## Catalog No. TH3224SS

Description: 200A 2P HD N4X SS 240V FUSIBLE

UPC No 783164089202

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	240 AC
Amperage	200 A
Poles	2
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X Water/Dust-tight
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 1-ph	15.0 hp
250 Vdc	40.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	35.1 in
Depth	5.2 in
Width	14.5 in
Weight	33.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">Spec-Setter Safety Switches</a> 36 page brochure and application guide. General Electric's Spec-Setter safety switches are available for all your disconnect needs, no matter what the application. <a href="#">200A (incl. 316 Stainless) - Safety Switches</a>	DET-845	Brochures
1 page outline drawing in .pdf format. <a href="#">Stainless Steel Safety Switches Sealed Tight - Latch it!</a>	10103091-SH113	Drawings-Outline and Dimensional
2 pages. New over center latch system requires no tools to open the switch. Designed for commercial and industrial applications in corrosive environments where safety, high performance and continuity of service are essential.	DET-842	Brochures

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.