



Catalog No. TH3362SS316

Description: 60A 3P HD N4X SS316 600V FUSIBLE

UPC No 783164382327

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 4X enclosure grade 316 stainless steel.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X (316 Stainless)
Options	None
Wire Range (Cu/Al)	14-2
480 Vac, NEC Std, 1-ph	5
480 Vac, NEC Std, 3-ph	15
480 Vac, Time Delay, 1-ph	20
480 Vac, Time Delay, 3-ph	30
600 Vac, NEC Std, 1-ph	3
600 Vac, NEC Std, 3-ph	15
600 Vac, Time Delay, 1-ph	25
600 Vac, Time Delay, 3-ph	50
125 Vdc	5
250 Vdc	10
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	19.3
Depth	5.2
Width	9.4
Weight	23

Publications

Title	Publication No.	Publication Type
60A (incl. 316 Stainless) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH109	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.