



Catalog No. TH3363MSS

Description: 100A 3P MD N4X SS 600V FUSIBLE

UPC No 783164102253

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Mill

- Designed specifically for the rugged conditions found in steel mills, cement foundries and other process-related environments.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating - field convertible to compression connectors.
- Full cover interlocks.

Descriptors

Category	Mill
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	100 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X Water/Dust-tight
Options	None
Wire Range (Cu/Al)	14-1/0 CU;12-1/0 AL
480 Vac, NEC Std, 1-ph	10.0 hp
480 Vac, NEC Std, 3-ph	25.0 hp
480 Vac, Time Delay, 1-ph	30.0 hp
480 Vac, Time Delay, 3-ph	60.0 hp
600 Vac, NEC Std, 1-ph	15.0 hp
600 Vac, NEC Std, 3-ph	30.0 hp
600 Vac, Time Delay, 1-ph	40.0 hp
600 Vac, Time Delay, 3-ph	75.0 hp
600 Vdc	20.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	25.4 in
--------	---------

Dimensions

Depth	5.0 in
Width	13.4 in
Weight	23.0 lb

Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH128	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.