



Catalog No. TH3363SS316

Description: 100A 3P HD N4X SS316 600V FUSIBLE

UPC No 783164382334

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 4X enclosure grade 316 stainless steel.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	100 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X (316 Stainless)
Options	None
Wire Range (Cu/Al)	14-1/0 CU;12-1/0 AL
480 Vac, NEC Std, 1-ph	10
480 Vac, NEC Std, 3-ph	25
480 Vac, Time Delay, 1-ph	30
480 Vac, Time Delay, 3-ph	60
600 Vac, NEC Std, 1-ph	3
600 Vac, NEC Std, 3-ph	30
600 Vac, Time Delay, 1-ph	40
600 Vac, Time Delay, 3-ph	75
250 Vdc	20
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	25.4
--------	------

Dimensions

Depth	5.2
Width	13.4
Weight	36

Publications

Title	Publication No.	Publication Type
200A (incl. 316 Stainless) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH113	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.