



## Catalog No. TH3364M

Description: 200A 3P MD N12 600V FUSIBLE

UPC No 783164092721

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Mill

- Designed specifically for the rugged conditions found in steel mills, cement foundries and other process-related environments.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating - field convertible to compression connectors.
- Full cover interlocks.

### Descriptors

Category	Mill
GO Schedule	SB

### Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 12 Drip/Dust-tight
Options	None
Wire Range (Cu/Al)	2-250
480 Vac, NEC Std, 1-ph	25.0 hp
480 Vac, NEC Std, 3-ph	50.0 hp
480 Vac, Time Delay, 1-ph	50.0 hp
480 Vac, Time Delay, 3-ph	125.0 hp
600 Vac, NEC Std, 1-ph	30.0 hp
600 Vac, NEC Std, 3-ph	60.0 hp
600 Vac, Time Delay, 1-ph	50.0 hp
600 Vac, Time Delay, 3-ph	150.0 hp
600 Vdc	40.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	No
UL Listed	Yes

### Dimensions

Height	35.1 in
Depth	5.0 in

## Dimensions

Width	14.4 in
Weight	45.0 lb

## Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH128	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.