



## Catalog No. TH3364SS316

Description: 200A 3P HD N4X SS316 600V FUSIBLE

UPC No 783164382341

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 4X enclosure grade 316 stainless steel.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X (316 Stainless)
Options	None
Wire Range (Cu/Al)	2-250
480 Vac, NEC Std, 1-ph	25
480 Vac, NEC Std, 3-ph	50
480 Vac, Time Delay, 1-ph	50
480 Vac, Time Delay, 3-ph	125
600 Vac, NEC Std, 1-ph	3
600 Vac, NEC Std, 3-ph	60
600 Vac, Time Delay, 1-ph	50
600 Vac, Time Delay, 3-ph	150
250 Vdc	40
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	35.1
--------	------

## Dimensions

Depth	5.2
Width	14.5
Weight	49

## Publications

Title	Publication No.	Publication Type
<a href="#">200A (incl. 316 Stainless) - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH113	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.