

111-85019

Article Number: 111-85019

Description: Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg



Base Data	Local Order Number	IT50R9C2
	Type	IT50R
	Color	Natural (NA)
	Features and Benefits	<ul style="list-style-type: none"> • Identification plate feature allows bundles to be easily marked and identified. • Wire and cable harnesses can be secured and identified using just one product, which saves time. • Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
	Quantity Per	bag
	Product Description	HellermannTyton Identification cable ties feature an identification plate allowing wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.
	Short Description	Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg
Product Dimensions	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	203.0mm
	Fixation Method	None
	Identification Plate Position	attached to bundle
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	1.1"
	Width W (Metric)	28.0mm
	Width W2 (Imperial)	0.18"
	Width W2 (Metric)	4.6mm
	Height H (Imperial)	0.51"

111-85019



Product Dimensions	Height H (Metric)	12.9mm
	Height of printable area (metric)	12.8mm
	Bundle Diameter Min. (Imperial)	0.37"
	Bundle Diameter Min. (Metric)	9.5mm
	Bundle Diameter Max. (Imperial)	1.8"
	Bundle Diameter Max. (Metric)	44.5mm
	Outside Diameter Min. (Imperial)	0.37"
	Outside Diameter Min. (Metric)	9.50mm
	Outside Diameter Max. (Imperial)	1.73"
	Outside Diameter Max. (Metric)	44.50mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2
	Width of Printable Area (imperial)	1.1"
	Width of printable area (metric)	28.00mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	US MILSPEC	MS3368-1-9A
	Flammability	UL94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 746B
UL Recognized (US and Canada)	Yes	
Logistic and Packaging		
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	1.5kg