



Catalog No. THN3362JCH

Description: 60A 3P HD N5/12 600V NONFUSE RECPT

UPC No 783164126662

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed specifically for industrial welding applications.
- Incorporates Crouse Hinds interlocked receptacle (mating CH plugs sold separately).
- Listed to UL standard 98 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- Enclosure has no knockouts.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 5, 12 Drip/Dust-tight
Options	Crouse-Hinds Interlock
Wire Range (Cu/Al)	12-2
240 Vac, NEC Std, 1-ph	10
240 Vac, NEC Std, 3-ph	20
480 Vac, NEC Std, 1-ph	20
480 Vac, NEC Std, 3-ph	50
600 Vac, NEC Std, 1-ph	25
600 Vac, NEC Std, 3-ph	60
250 Vdc	10
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	19.3
Depth	5.7
Width	9.4
Weight	21

Publications

Title	Publication No.	Publication Type
CHSS suffix) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH132	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.