



- **Molded from a nylon material which, in the event of a fire, will not burn and will not produce toxic gases.** Also formulated for sunlight resistance. Other Heyco products are available in this material—please consult Heyco.
- Close unneeded panel holes.
- Quick and easy installation.
- Convex, matte finish head tapers to a thin edge (Except HFP-187 glossy finish).
- Lock firmly into panel up to .125” (3,2 mm) thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Approximate Head Thickness: .062” (1,6 mm). Thickness may vary.
- Multiple sizes for use in .187” (4,7 mm) to 2.000” (50,8 mm) diameter holes. Consult Heyco for larger sizes.

## Heyco® Halogen and Phosphorus-Free 94V-0 Hole Plugs

Heat Stabilized • Self Extinguishing • Nontoxic • UV Resistant  
 Mounting Hole Diameter Range: .187” (4,7 mm) to 2.000” (50,8 mm)

| MOUNTING HOLE DIAMETER |     | PART NO. | DESCRIPTION | PART DIMENSIONS |                    |     |                     |
|------------------------|-----|----------|-------------|-----------------|--------------------|-----|---------------------|
| in.                    | mm. |          |             | Black           | A<br>Head Diameter |     | B<br>Overall Height |
|                        |     |          |             | in.             | mm.                | in. | mm.                 |

Single Locking Step for Panel Thickness up to .062” (1,6 mm)

|      |     |             |          |     |     |     |     |
|------|-----|-------------|----------|-----|-----|-----|-----|
| .187 | 4,7 | <b>2593</b> | HFP 187* | .25 | 6,4 | .24 | 6,1 |
| .250 | 6,4 | <b>2606</b> | HFP 250  | .31 | 7,9 | .31 | 7,9 |
| .312 | 7,9 | <b>2616</b> | HFP 312  | .38 | 9,5 |     |     |

Multiple Locking Steps for Panel Thickness up to .125” (3,2 mm)


|               |             |             |          |      |      |     |      |     |      |
|---------------|-------------|-------------|----------|------|------|-----|------|-----|------|
| .375          | 9,5         | <b>2623</b> | HFP 375  | .47  | 11,9 | .41 | 10,3 |     |      |
| .437          | 11,1        | <b>2636</b> | HFP 437  | .53  | 13,5 |     |      |     |      |
| .500          | 12,7        | <b>2646</b> | HFP 500  | .58  | 14,7 |     |      |     |      |
| .625          | 15,9        | <b>2666</b> | HFP 625  | .72  | 18,2 |     |      |     |      |
| .750          | 19,1        | <b>2686</b> | HFP 750  | .92  | 23,4 |     |      |     |      |
| .875          | 22,2        | <b>2706</b> | HFP 875  | 1.02 | 25,8 | .45 | 11,5 |     |      |
| 1.000         | 25,4        | <b>2716</b> | HFP 1000 | 1.20 | 30,6 |     |      |     |      |
| 1.093 - 1.125 | 27,8 - 28,6 | <b>2729</b> | HFP 1093 | 1.22 | 30,9 |     |      |     |      |
| 1.250         | 31,7        | <b>2749</b> | HFP 1250 | 1.38 | 34,9 |     |      |     |      |
| 1.375         | 34,9        | <b>2759</b> | HFP 1375 | 1.50 | 38,1 |     |      |     |      |
| 1.500         | 38,1        | <b>2769</b> | HFP 1500 | 1.69 | 42,8 |     |      |     |      |
| 1.750         | 44,5        | <b>2779</b> | HFP 1750 | 1.92 | 48,7 |     |      |     |      |
| 2.000         | 50,8        | <b>2789</b> | HFP 2000 | 2.17 | 55,1 |     |      |     |      |
|               |             |             |          |      |      |     |      | .47 | 11,9 |

Multiple Locking Steps for Panel Thickness up to .250” (6,4 mm)


**ALL NEW PRODUCTS**

|             |           |              |            |      |      |     |      |
|-------------|-----------|--------------|------------|------|------|-----|------|
| .500        | 12,7      | <b>3004F</b> | HFPT 500   | .58  | 14,7 | .56 | 14,3 |
| .625        | 15,9      | <b>3006F</b> | HFPT 625 * | .73  | 18,5 | .52 | 13,2 |
| .750        | 19,1      | <b>3008F</b> | HFPT 750 * | .91  | 23,1 | .56 | 14,3 |
| .875        | 22,2      | <b>3044F</b> | HFPT 875   | 1.02 | 25,8 |     |      |
| 1.000       | 25,4      | <b>3046F</b> | HFPT 1000  | 1.20 | 30,6 |     |      |
| 1.093-1.125 | 27,8-28,6 | <b>3018F</b> | HFPT 1093  | 1.22 | 30,9 |     |      |
| 1.250       | 31,7      | <b>3102F</b> | HFPT 1250  | 1.38 | 34,9 |     |      |
| 1.375       | 34,9      | <b>3106F</b> | HFPT 1375  | 1.50 | 38,1 |     |      |
| 1.500       | 38,1      | <b>3048F</b> | HFPT 1500  | 1.67 | 42,4 |     |      |
| 1.750       | 44,5      | <b>3027F</b> | HFPT 1750  | 1.91 | 48,4 |     |      |
| 2.000       | 50,8      | <b>3050F</b> | HFPT 2000  | 2.17 | 55,1 |     |      |
|             |           |              |            |      |      |     |      |

Standard color black.  
 \*Convex, glossy finish head.



**SINGLE PANEL THICKNESS DESIGN**



**MULTIPLE PANEL THICKNESS DESIGN**

*Quick Specs*

|                     |  |
|---------------------|--|
| Material            | Nylon 6/6  |
| Certifications      | Recognized under the Component Program of Underwriters' Laboratories File E51579 |
|                     | Certified by the Canadian Standards Association File 8919                        |
| Flammability Rating | 94V-0  |
| Temperature Range   | -40°F (-40°C) to 221°F (105°C)   |