


## Terminal Strips

- Heavy-duty, corrosion-resistant screws, surface plates and optional hardware
- Accessory hardware provides a variety of termination options
- Available cover helps prevent contact with live terminals

### 89-200 Series Terminal Strips 30A/600V\* UL/CSA

- .562 in. (14.28mm) center spacing
- Accepts wire sizes from 22 through 10 AWG Cu
- #8-32 phillslot, zinc-plated steel terminal screws (Recommended torque: 16 in. - lb.)



No. of Poles	Dimensions (Inches)		Cat. No.
	A	B	
2	2.13	1.69	89-202
3	2.69	2.25	89-203
4	3.25	2.81	89-204
6	4.37	3.94	89-206
8	5.50	5.06	89-208
10	6.62	6.19	89-210
12	7.75	7.31	89-212


\*Max. electrical rating 30A/250V when used with optional quick-connects.



- Rugged polyester thermoplastic base (UL Rated 94V-O)
- Operating temperature rated from 130°C (260°F) to -40°C (-40°F)
- UL Recognized (E62622) and CSA Certified (LR15364)

### 89-300 Series Terminal Strips 15A/250V\*\* UL, 15A/150V\*\* CSA

- .375 in. (9.52mm) center spacing
- Accepts wire sizes from 22 through 14 AWG Cu
- #6-32 phillslot, zinc-plated steel terminal screws (Recommended torque: 9 in. - lb.)



No. of Poles	Dimensions (Inches)		Cat. No.
	A	B	
2	1.40	1.12	89-302
4	2.16	1.88	89-304
6	2.90	2.62	89-306
8	3.66	3.38	89-308
10	4.40	4.12	89-310
12	5.16	4.88	89-312

\*\*Max. electrical rating 15A/125V when used with optional quick-connects.

