



Catalog No. THQC2120LL

Description: 2 POLE 120/240V 10KA 20A W/NO LUGS

UPC No 783164109184

Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories.

Descriptors

| | |
|-------------|-----------------------------------|
| Category | Q-Line Miniature Circuit Breakers |
| GO Schedule | EB |

Specifications

| | |
|---------------------------------|----------------------|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 20 A |
| System Voltage | 120 Vac, 120/240 Vac |
| Poles | 2 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Product Line | Q-Line (Lug-Lug) |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

Publications

| Title | Publication No. | Publication Type |
|--|-----------------|----------------------------------|
| Q-Line Lug-Lug, Din Rail Mountable MCCB, 100A Frame 2- Pole , Drawing 1-Page fully dimensioned outline drawing in .pdf format | 208C3604-SH2 | Drawings-Outline and Dimensional |

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.