

Vinyl Insulated Female Disconnects




Wire Range (AWG)	Wire Range (mm ²)	Tab Size (Inches)	Tab Size (mm)	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.	Ctn. Qty.	Cat. No.
						L	B	W	F	L	B	W	L				
22 – 18	0.5 – 1.0	.110 x .020	2.8 x 0.5	.150	3.8	.728	.413	.126	.256	18.5	10.5	3.2	6.5	25	83-9511	—	—
16 – 14	1.5 – 2.5	.110 x .020	2.8 x 0.5	.185	4.7	.748	.413	.126	.256	19.0	10.5	3.2	6.5	25	83-9521	—	—
22 – 18	0.5 – 1.0	.187 x .020	4.75 x 0.5	.150	3.8	.764	.413	.197	.252	19.4	10.5	5.0	6.4	25	83-9541	—	—
16 – 14	1.5 – 2.5	.187 x .020	4.75 x 0.5	.185	4.7	.764	.413	.197	.252	19.4	10.5	5.0	6.4	25	83-9551	—	—
22 – 18	0.5 – 1.0	.250 x .032	6.35 x 0.8	.150	3.8	.819	.413	.260	.287	20.8	10.5	6.6	7.3	25	83-9571	—	—
16 – 14	1.5 – 2.5	.250 x .032	6.35 x 0.8	.185	4.7	.819	.413	.260	.287	20.8	10.5	6.6	7.3	25	83-9581	500	84-9581
14 – 12	2.5 – 4.0	.250 x .032	6.35 x 0.8	.244	6.2	.917	.512	.260	.287	23.3	13.0	6.6	7.3	25	83-9591	—	—
12 – 10	4.0 – 6.0	.250 x .032	6.35 x 0.8	.244	6.2	.917	.512	.260	.287	23.3	13.0	6.6	7.3	25	83-9601	—	—

75° C/300 Volts max.

Listed 774A Cu Only Pressure Wire Connector

Vinyl Insulated Male Disconnects




Wire Range (AWG)	Wire Range (mm ²)	Tab Size (Inches)	Tab Size (mm)	Max. Wire Ins. Dia. (Inches)	Max. Wire Ins. Dia. (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.
						L	B	W	F	L	B	W	F		
22 – 18	0.5 – 1.0	.250 x .032	6.35 x 0.8	.150	3.8	.858	.413	.250	.303	21.8	10.5	6.35	7.7	25	83-9971
16 – 14	1.5 – 2.5	.250 x .032	6.35 x 0.8	.185	4.7	.858	.413	.250	.303	21.8	10.5	6.35	7.7	25	83-9981
12 – 10	4.0 – 6.0	.250 x .032	6.35 x 0.8	.244	6.2	.945	.512	.250	.303	24.0	13.0	6.35	7.7	25	83-9991

75° C/300 Volts max.

Listed 774A Cu Only Pressure Wire Connector

Non-Insulated Female Disconnects



Wire Range (AWG)	Wire Range (mm ²)	Tab Size (Inches)	Tab Size (mm)	Dimensions (Inches)				Dimensions (mm)				Ctn. Qty.	Cat. No.
				L	B	W	F	L	B	W	F		
22 – 18	0.5 – 1.0	.110 x .020	2.8 x 0.5	.630	.189	.126	.256	16.0	4.8	3.2	6.5	25	83-9411
16 – 14	1.5 – 2.5	.110 x .020	2.8 x 0.5	.630	.189	.126	.256	16.0	4.8	3.2	6.5	25	83-9421
22 – 18	0.5 – 1.25	.187 x .020	4.75 x 0.5	.630	.189	.197	.252	16.0	4.8	5.0	6.4	25	83-9441
16 – 14	1.5 – 2.5	.187 x .020	4.75 x 0.5	.630	.189	.197	.252	16.0	4.8	5.0	6.4	25	83-9451
22 – 18	0.5 – 1.25	.250 x .032	6.35 x 0.8	.630	.189	.260	.287	16.0	4.8	6.6	7.3	25	83-9471
16 – 14	1.5 – 2.5	.250 x .032	6.35 x 0.8	.630	.189	.260	.287	16.0	4.8	6.6	7.3	25	83-9481
12 – 10	4.0 – 6.0	.250 x .032	6.35 x 0.8	.728	.236	.260	.287	18.5	6.0	6.6	7.3	25	83-9501

105° C/300 Volts max.