



MATERIAL SAFETY DATA SHEET

GENERAL INFORMATION

PRODUCT NAME OR NUMBER (as it appears on label) Buchanan B-Cap® Wire-Connector – all models		CATALOG NUMBER B1-xx, B2-xx, B4-xx, BGr-xx
MANUFACTURER'S NAME IDEAL INDUSTRIES, INC.		EMERGENCY TELEPHONE NO. (815) 895-5181
ADDRESS (Number, Street, City, State, Zip Code) Becker Place, Sycamore, IL 60178		
HAZARDOUS MATERIAL DESCRIPTION, PROPER SHIPPING NAME, HAZARD CLASS, HAZARD CLASS, HAZARD ID NO. (49 CFR 172.101) None		
CHEMICAL DESCRIPTION Polyamide, Zinc Plated Steel	FORMULA Proprietary	

SECTION I - INGREDIENTS

CAS REGISTRY NO.	%W	CHEMICAL NAME(S)*	Listed as a carcinogen in NTP, IARC or OSHA 1910(z) (specify)
32131-17-2	<55	Polyhexymethylene Adipamide	No
7439-89-6	<50	Steel	No
7440-66-6	<2	Zinc	No

SECTION II - PHYSICAL DATA

BOILING POINT N/A °F °C	SPECIFIC GRAVITY (H ₂ O=1) >1	PERCENT VOLATILE BY VOLUME (%) <1
SOLUBILITY IN WATER Insoluble	pH = N/A	PERCENT SOLID BY WEIGHT (%) ~100
APPEARANCE AND ODOR	IS MATERIAL: LIQUID <input checked="" type="checkbox"/> SOLID <input type="checkbox"/> GEL GAS <input type="checkbox"/> PASTE	

SECTION III - FIRE AND EXPLOSION HAZARD DATA

FLASH POINT None	method used C.O.C.	FLAMMABLE LIMITS	LEL None	UEL None
EXTINGUISHING MEDIA None Normally Required				
SPECIAL FIRE FIGHTING PROCEDURES Use extinguishing media for surrounding materials				
UNUSUAL FIRE AND EXPLOSION HAZARDS Use self-contained breathing apparatus with full face shield				
Polyamide material is a UL listed 94 V-2 flame rated product.				

* None of the chemical raw materials contained in this formulation are considered hazardous under the Federal Hazards Communication Standard 29 C. F. R 1910.1200

SECTION IV - HEALTH HAZARD INFORMATION

EFFECTS OF OVEREXPOSURE - Conditions to Avoid	Prolonged repeated skin contact with grease may slight skin discomfort
THRESHOLD LIMIT VALUE	N/F
PRIMARY ROUTES OF ENTRY Inhalation <input type="checkbox"/> Skin Contact <input checked="" type="checkbox"/> Other (specify) _____ Ingestion _____	
EMERGENCY FIRST AID PROCEDURES	See other precautions at bottom of page.
SKIN CONTACT:	
EYE CONTACT:	None
INGESTION:	Consult Physician

SECTION V - REACTIVITY DATA

STABILITY	UNSTABLE		CONDITIONS TO AVOID	Direct exposure to flame or excessive heat.
	STABLE	X		
INCOMPATIBILITY (materials to avoid)				
Strong Oxidizing agents				
HAZARDOUS DECOMPOSITION PRODUCTS:				
Oxides of Carbon				
HAZARDOUS POLYMERIZATION	MAY OCCUR		CONDITIONS TO AVOID	None
	WILL NOT OCCUR	X		

SECTION VI - SPILL AND LEAK PROCEDURES

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED		Sweep up to prevent tripping	
WASTE DISPOSAL METHOD		Landfill or incinerate in accordance with local, state and federal guidelines	
CERCLA (Superfund) REPORTABLE QUANTITY (in lbs)			
N/A			
RCRA HAZARDOUS WASTE NO. (40CFR 261.33)			
N/A			
VOLATILE ORGANIC COMPOUND (VOC) (as packaged, minus water)			
N/A			
* Theoretical _____ lb/gal		NA	* Analytical _____ lb/gal
			N/A

SECTION VII - PERSONAL PROTECTION INFORMATION

RESPIRATORY PROTECTION (specify type)			
None normally required			
VENTILATION	LOCAL EXHAUST (Specify Rate)	None normally required.	SPECIAL N/A
	MECHANICAL (General) (Specify Rate)	Recommended in closed areas.	OTHER N/A
PROTECTIVE GLOVES (specify type)		EYE PROTECTION (specify type)	
		Per company policy	
OTHER PROTECTIVE EQUIPMENT			
None			

SECTION VIII - SPECIAL PRECAUTIONS

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING	Avoid excessive heat or open flames
OTHER PRECAUTIONS	None

SECTION IX - ADDITIONAL INFORMATION

None

N/A = Not Applicable, N.E. = None Established

THIS MATERIAL SAFETY DATA SHEET PREPARED BY:

NAME	James R. MacMurdo	SIGNATURE <i>James R. MacMurdo</i>
TITLE	Director, Corporate Quality Assurance	
DATE	03/10/2006	