

IDEAL® WIRE TERMINATION



Based on 2011 data available from Epicor/Vista.

powerplug® Luminaire Disconnects







The PowerPlug® allows safe disconnect of hot and neutral ballast wiring.

- Meets new NEC and CEC code changes for non-residential fluorescent luminaires
- Perfect for OEM new lighting installations or retrofit lighting applications
- Meets UL and CSA finger-probe safety requirements
- Allows safe disconnect of hot and neutral ballast wiring

PowerPlug® Selection Chart		
Application	New Installations	Retrofits
For 1-ballast fixtures	102	102, 182
For 2-ballast, dimming and switching fixtures	103	103, 183



Model	Color	Electrical Rating	Wire Range	Line Side	Ballast Side	Quantity	Cat. No.
102 2-wire 	Orange	6 Amps/600 Volts Max.	Solid	#12 – #18		Card of 25	30-372
			Stranded	#12 – #14 (≤19 str.)		Jar of 75	30-382J
			Stranded Tin-Bonded	#12 – #14 (≤19 str.)		Jar of 150	30-352J
				#16 (≤26 str.) #18 (≤16 str.)		Box of 1,000	30-102
103 3-Wire 	Orange	6 Amps/600 Volts Max.	Solid	#12 – #18	#18	Card of 20	30-383X
			Stranded	#12 – #14 (≤19 str.)		Jar of 50	30-383XJ
			Stranded Tin-Bonded	#12 – #14 (≤19 str.)	#18 (≤16 str.)	Jar of 100	30-353XJ
				#16 (≤26 str.) #18 (≤16 str.)		Box of 1,000	30-103X
182 2-wire 	Orange	3 Amps 120V 1.3 Amps 277V 1 Amps 347V	Solid	#18		Box of 100	30-082
						Box of 2,500	30-682
183 3-Wire 	Orange	0.75 Amps 480V 0.60 Amps 600V	Solid	#18		Box of 1,000 w/6" leads	30-682L
						Box of 100	30-083
						Box of 2,500	30-683

1,000V maximum fixtures and signs.

SpliceLine® In-Line Wire Connectors


The SpliceLine® is a crimp-free, push-in wire connector that installs in half the time of a traditional butt splice. Perfect for lengthening a short wire in a box, for pre-fab operation or for surface raceway wiring. SpliceLine® accepts solid and stranded wire, is UL Listed and is made in the U.S.A.

- Crimp-free, push-in butt splice
- Easily passes through 1/2 in. knockouts
- End-to-end connection ideal for pre-fab operations
- Transparent polycarbonate window for visual inspection of connection
- Wide wire range of: 12 – 20 AWG solid & 12 – 16 AWG stranded



FAST FACT:

Perfect for lengthening short wires, the SpliceLine™ is 2X faster than traditional butt-splices

Model	Color	Rating	Wire Range	Quantity	Cat. No.
42 	Orange	600V/20A 105°C	Solid: #12 – #20	Card of 10	30-1742
			Stranded: #12 – #16 (≤19 str.)	Box of 100	30-1042
			Stranded Tin-Bonded: #14 – #18 (≤19 str.)	Jar of 300	30-1042J
				Box of 2,500	30-1642

