



Quick Change Screwdriver

- Patented Sure-Loc™ Quick Change chuck eliminates debris pick up as well as dropped bits
- Built-in bit storage container in handle holds up to five extra insert bits
- Bits fit all standard multi-bit screwdrivers
- E-Z Spin™ high torque rotating flip cap
- Patented design



(Lifetime warranty excludes bits)

See website for complete listing of bits in blocks.

Description	Blade Length	Handle Length	Overall Length	Cat. No.
33-Piece Quick Change Screwdriver Set - Quick Change Screwdriver and 32-Piece Tamper-Proof Bit Block	3-1/16 in.	4-3/16 in.	7-1/4 in.	35-933
32-Piece Tamper-Proof Bit Block				35-933TP
32-Piece Standard Bit Block				35-933STD



4-Piece Mini Cushioned-Grip Screwdriver Set

SOLD ONLY AS A SET



Slim Electronics

- Designed for maximum handling comfort when working in tight areas
- Tough, chrome vanadium steel shank
- Phosphate tip for longer wear life
- Rotating cap for optimum control for precise centering
- Color-coded cap for easy identification



Description	Blade Length	Handle Length	Overall Length	Cat. No.
Phillips, #0	2-31/32 in.	2-3/4 in.	5-23/32 in.	-
Keystone, 1/16 in.	1-31/32 in.	2-3/4 in.	4-23/32 in.	-
Cabinet, 3/32 in.	2-31/32 in.	2-3/4 in.	5-23/32 in.	-
Cabinet, 1/8 in.	2-31/32 in.	2-3/4 in.	5-23/32 in.	-
4-Piece Set				35-1301

Description	Blade Length	Handle Length	Overall Length	Cat. No.
Cabinet, 3/32 in.	2-1/2 in.	3-9/16 in.	6-1/16 in.	36-240
Cabinet, 3/32 in.	3 in.	3-9/16 in.	6-9/16 in.	36-241
Cabinet, 1/8 in.	4 in.	3-9/16 in.	7-9/16 in.	36-242
Cabinet, 1/8 in.	6 in.	3-9/16 in.	9-9/16 in.	36-243
Cabinet, 5/32 in.	4 in.	3-9/16 in.	7-9/16 in.	36-244
Cabinet, 5/32 in.	6 in.	3-9/16 in.	9-9/16 in.	36-245
Phillips, #0	2-1/2 in.	3-9/16 in.	6-1/16 in.	36-246
7-Piece Set includes one each of 36-240 thru 36-246				36-248
4-Piece Set includes one each of 36-240, -241, -242, & -246				36-249

2-Piece Stubby Screwdriver Set



Description	Blade Length	Handle Length	Overall Length	Cat. No.
2-Piece Screwdriver Set	1-1/2 in.	2-1/8 in.	3-5/8 in.	35-1300