



GE
Lighting

10086 - GE Cool White T5

F13T5/CW

Product Photo



GENERAL CHARACTERISTICS

Base Description	Miniature Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	6 mg
Mercury-Picogram per mean lm hr	1702.1
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	5000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G5
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	705 lm
Nominal Initial Lumen per Watt	65
Initial Lumens-nominal	850 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10086
Description	F13T5/CW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168100861
Standard Package GTIN	10043168100868
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168100861

DIMENSIONS

Bulb Diameter (DIA) <Max>	0.63 in
Bulb Diameter (DIA) <Min>	0.53 in
Diameter	0.62 in
Face to End of Opposing Pin (B) <Max>	20.63 in
Face to End of Opposing Pin (B) <Min>	20.53 in
Nominal Length	21.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	180.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	13 W



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jul 12, 2017 4:21:17 PM For additional information, visit www.gelighting.com