



GE
Lighting

25611 - GE Ecolux® Starcoat® T8

F32T8/SPX30/ECO

☞ Passes TCLP, which can lower disposal costs.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	34.5
Rated Life Instant Start-Hrs	21000 h @ 3 h 30000 h @ 12 h
Rated Life Rapid Start - Hrs	30000 h @ 3 h 36000 h @ 12 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	30000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2800 lm
Nominal Initial Lumen per Watt	92
Initial Lumens-nominal	2925 lm
Color Rendering Index-CRI	85
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	25611
Description	F32T8/SPX30/ECO
Alternative Unit Of Measure	CASE

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	47.67 in
Face to End of Opposing Pin (B) <Max>	47.5 in
Face to End of Opposing Pin (B) <Min>	47.4 in
Nominal Length	48.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	315.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	32 W

CAUTIONS & WARNINGS



Warning


Risk of Electric Shock

- Turn power off before inspection
- installation or removal.

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.





Aug 18, 2016 6:56:33 PM For additional information, visit www.gelighting.com