

PAR LINE



PAR38 17W



PAR38 17W GU24



PATENT PENDING REFINE OPTIC



WATCH THE VIDEO









REFLECTOR
Directs lightFOCUS LENS
Focuses center beamSHAPING LENS
Refines beam pattern

High CRI 90, R9 50 & R13 90

High candela to lumen ratio

Suitable for use in enclosed fixtures

● Black finish

Model	Product	CCT	Lumens (lm)	CBCP (cd)	Equiv.	
 PAR38 17W	18.5PAR38G4DIM/927SP15	16147	2700K	950	10,500	100W ✓
	18.5PAR38G4DIM/927NF25	16148	2700K	1105	5800	120W ✓
	17PAR38G4DIM/927FL40	16149	2700K	1105	2400	120W ✓
	18.5PAR38G4DIM/930SP15	16150	3000K	1000	11,000	100W ✓
	18.5PAR38G4DIM/930NF25	16151	3000K	1150	5900	120W ✓
	17PAR38G4DIM/930FL40	16152	3000K	1150	2500	120W ✓
	17PAR38G4DIM/940FL40	16155	4000K	1200	2650	120W ✓
	18.5PAR38G4DIM/930SP15/B ●	16256	3000K	1000	11,000	100W ✓
	18.5PAR38G4DIM/930NF25/B ●	16257	3000K	1150	5900	120W ✓
	17PAR38G4DIM/930FL40/B ●	16258	3000K	1150	2500	120W ✓
 PAR38 17W 277V	17PAR38G4/930FL40/277V	16161	3000K	1150	2500	120W ✓
	17PAR38G4/940FL40/277V	16164	4000K	1200	2650	120W ✓
 PAR38 17W GU24	17PAR38G4DIM/927FL40/GU24	16303	2700K	1105	2400	120W ✓
	17PAR38G4DIM/930FL40/GU24	16306	3000K	1150	2500	120W ✓
 PAR30 12.5W	14.5PAR30G4DIM/927SP15	16111	2700K	725	6155	75W ✓
	12.5PAR30G4DIM/927NF25	16112	2700K	815	3350	75W ✓
	12.5PAR30G4DIM/927FL40	16113	2700K	815	1750	75W ✓
	14.5 PAR30G4DIM/930SP15	16114	3000K	760	6250	75W ✓
	12.5PAR30G4DIM/930NF25	16115	3000K	850	3600	75W ✓
	12.5PAR30G4DIM/930FL40	16116	3000K	850	1850	75W ✓
	12.5PAR30G4DIM/940FL40	16119	4000K	900	2050	75W ✓
	14.5PAR30G4DIM/930SP15/B ●	16208	3000K	760	6250	75W ✓
	12.5PAR30G4DIM/930NF25/B ●	16209	3000K	850	3600	75W ✓
	12.5PAR30G4DIM/930FL40/B ●	16210	3000K	850	1850	75W ✓
 PAR30 12.5W 277V	12.5PAR30G4/930FL40/277V	16125	3000K	850	1850	75W ✓
	12.5PAR30G4/940FL40/277V	16128	4000K	900	2050	75W ✓
 PAR30 12.5W GU24	12.5PAR30G4DIM/927FL40/GU24	16279	2700K	815	1750	75W ✓
	12.5PAR30G4DIM/930FL40/GU24	16282	3000K	850	1850	75W ✓
	12.5PAR30G4DIM/927FL40/GU24/B ●	16291	2700K	815	1750	75W ✓
 PAR30SN 11W	14PAR30SNG4DIM/927SP15	16129	2700K	700	6155	75W ✓
	11PAR30SNG4DIM/927NF25	16130	2700K	705	2910	75W ✓
	11PAR30SNG4DIM/927FL40	16131	2700K	705	1400	75W ✓
	14PAR30SNG4DIM/930SP15	16132	3000K	725	6200	75W ✓
	11PAR30SNG4DIM/930NF25	16133	3000K	740	2910	75W ✓
	11PAR30SNG4DIM/930FL40	16134	3000K	740	1450	75W ✓
	11PAR30SNG4DIM/940FL40	16137	4000K	780	1500	75W ✓
	14PAR30SNG4DIM/930SP15/B ●	16232	3000K	725	6200	75W ✓
	11PAR30SNG4DIM/930NF25/B ●	16233	3000K	740	2910	75W ✓
	11PAR30SNG4DIM/930FL40/B ●	16234	3000K	740	1450	75W ✓
 PAR20 7W	7PAR20G4DIM/927FL40	16108	2700K	460	600	50W ✓
	7PAR20G4DIM/930FL40	16109	3000K	480	650	50W ✓
	7PAR20G4DIM/940FL40	16110	4000K	505	700	50W ✓
	7PAR20G4DIM/930FL40/B ●	16202	3000K	480	650	50W ✓