

## TYPE CO

### Features

- Manufactured from electrolytic seamless copper tubing
- Compact design
- Range taking
- Re-usable
- Suitable for use in circuits rated 35KV or less, proper high voltage spacing and insulation techniques must be used
- Bossed mounting holes
- Rated for 90° C

### Benefits

- Provides maximum conductivity and strength
- Saves space and reduces installation time
- Permits inventories to be kept to a minimum
- Provides efficient use and flexibility in the field
- Application versatility
- Acts as an anti-rotation device and prevents the connector from turning



Fig. 1

Fig. 2

Fig. 3

Fig. 4

Fig. 5

Fig. 6

Fig. 7

Catalog Number	Figure Number	Wire Range	Dimensions							
			L	W	Height With Maximum Wire	Bossed Mounting Hole Tapped	Style Boss And Outside Dimensions	Top Hole Tapped	Top Hole And Inner Side Walls Tapped	Bottom Clearance Hole
CO3RP	1	6-14	3/8	11/32	21/32	8-32	Round .216-.220	1/4-28	-	-
CO3SP	1	6-14	3/8	11/32	21/32	10-32	Square .216-.220	1/4-28	-	-
CO4RP	2	4-14	15/32	29/64	19/32	10-32	Round .227-.231	5/16-24	-	-
CO4SP	2	4-14	15/32	29/64	19/32	10-32	Square .227-.231	5/16-24	-	-
CO4CW	3	4-14	15/32	29/64	3/4	-	-	-	3/8-27	.203
CO4CP	7	4-14	15/32	29/64	21/32	-	-	5/16-24	-	.265
CO4DD	5	4-14	29/32	29/64	19/32	10-32	Round .227-.231	5/16-24	-	-

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)  
Tested to UL 486A/B, UL File E6207