

MBT8S-S

Stainless Steel Tie, 7.9" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg

Article Number: 111-93088

Part Number: MBT8S-S

Type: MBT8SS



Material	Stainless Steel (SS304)
Part No.	MBT8S-S
Type	MBT8SS
Color	Metal (ML)
Features	<ul style="list-style-type: none"> • 304 grade stainless steel offers excellent resistance to corrosion, weather and chemical resistance. • Ball bearing locking mechanism assures high tensile strength and easy insertion.
Min. Tensile Strength	202.0lbs / 900.0N
Length (L)	7.9" / 201.0mm
Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	1Pieces
EAN code	5022660143663
Flammability	non-burning
Identification Plate Position	none
Material Specification	LFH
Operating Temperature	-112 °F to +1000 °F (-80 °C to +538 °C)
Releasable Closure (Yes/No)	No
Specification	BV
Tie Closure	ball bearing lock
Typical Application	Metal ties are predestinated for all areas with requirements for high holding force, reliability and fire resistance. The MBT range of stainless steel cable ties can be used in chemical industry and on oil platforms as well as in mass transit, shipbuilding and mining industry. MBT ties are also suitable for machine building, apparatus construction and in the outside area of radio technology. Additionally MBT ties are a good solution to fix lighting in theatres and exhibition halls.
UPC	089306203179
Variant	No Serration
Width (W)	0.18" / 4.6mm
Min. Ø Bundle	0.67" / 17.0mm
Max. Ø Bundle	2.0" / 50.0mm
Thickness	0.3mm