

156-00592

HellermannTyton



Article Number: 156-00592

Description: Cable Tie & Edge Clip, 8.0" Long, EC23, Panel Thickness .12"-.24", 50 lb, PA66UV, Black, 100/bag

Base Data	
Local Order Number	156-00592
Type	T50REC23
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
Quantity Per	bag
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Short Description	Cable Tie & Edge Clip, 8.0" Long, EC23, Panel Thickness .12"-.24", 50 lb, PA66UV, Black, 100/bag
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Length L (Imperial)	8.0"
Length L (Metric)	200mm
Length L2 (Imperial)	0.58"
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Identification Plate Position	none
Length L2 (Metric)	14.8mm
Variant	Inside Serrated
Width W (Imperial)	0.18"
Width W (Metric)	4.6mm
Width W2 (Imperial)	0.63"
Width W2 (Metric)	16.0mm
Height H (Imperial)	0.05"

156-00592



Product Dimensions	Height H (Metric)	1.2mm
	Height H2 (Imperial)	0.57"
	Height H2 (Metric)	14.6mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.0mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	45.0mm
	Panel Thickness Max. (Imperial)	0.24"
	Panel Thickness Max. (Metric)	6.00mm
	Panel Thickness Min. (Imperial)	0.12"
Panel Thickness Min. (Metric)	3.00mm	
Material and Specifications		
	Material	Polyamide 6.6 UV-stabilized (PA66UV)
	Material Shortcut	PA66HIRHSW
	Material Cable Tie	Polyamide 6.6 UV-stabilized (PA66UV)
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987