




Heyco® SunBundler® Stainless Steel Cable Ties

- **Extremely durable, vinyl jacketed Stainless Steel Cable Tie.**
- Smooth vinyl jacketing prevents damage to installation cable insulation.
- Stainless steel crimp sleeve for easy field installation with electrician linesman pliers, or wire cutters.
- UV protected vinyl jacket is excellent for solar installation where product durability is required.
- Use standard wire cutters to both crimp the sleeve and cut the excess wire.
- Constructed from Commercial Aircraft Grade Stainless wire with UV protected vinyl jacket.
- Not for use in a marine salt water environment. Contact Heyco for alternative materials

PART SPECIFICATIONS				PART NO.	DESCRIPTION	PART DIMENSIONS			
Minimum Tensile Strength		Maximum Bundle Diameter				A Length	B Diameter		in.
Lbs.	N	in.	mm.	in.	mm.		in.	mm.	
100	440	2.30	58,4	S6408	SunBundler® 8	8	203	.06	1,6
		2.92	74,2	S6410	SunBundler® 10	10	254		
		3.88	98,6	S6412	SunBundler® 12	12	305		
		4.20	106,7	S6414	SunBundler® 14	14	356		
		6.36	161,5	S6420	SunBundler® 20	20	508		

*Black vinyl jacketed 302/304 stainless steel wire.



Material

Commercial Aircraft Grade 302/304 stainless wire w/UV protected vinyl jacket and 304 stainless steel crimp sleeve




Heyco® SunWrap™ - Heavy Duty Cable Guard



- **Easy to use: Just twist on wire!**
- Designed to shield heavier cables and cable bundles; **extend cable life.**
- Available in a **variety of sizes** that fit cable and cable bundles from 3/4" to 6" in diameter.
- **Smooth finished interior wall.**
- **Highly flexible** for ease of movement.
- Packaged as one continuous piece in a box, not spooled.
- May be **cut to desired length**, please consult Heyco.

BUNDLE RANGE				PART NO.	DESCRIPTION	PART DIMENSIONS					
Minimum Diameter		Maximum Diameter				Black	A Outside Dia.		B Pitch		C Thickness
in.	mm.	in.	mm.		in.		mm.	in.	mm.	in.	mm.
.750	19,1	1.500	38,1	8964	CWG 99 PE	.93	23,6	.95	24,1	.12	3,0
1.000	25,4	2.000	50,8	8966	CWG 126 PE	1.12	28,4	1.25	31,8	.13	3,3
1.250	31,8	2.500	63,5	8968	CWG 153 PE	1.37	34,8	1.35	34,3	.14	3,5
1.500	38,1	3.000	76,2	8970	CWG 181 PE	1.62	41,1	1.50	38,1	.15	3,9
2.000	50,8	3.500	88,9	8972	CWG 234 PE	2.09	53,1	1.60	40,6	.17	4,3
3.500	88,9	6.000	152,4	8974	CWG 401 PE	3.50	88,9	1.95	49,5	.25	6,4

*Standard color black or color coded



Material
Temperature Range

High Density Polyethylene
0°F (-18°C) to 165°F (74°C)

Quick
Specs