




## Heyco® SunBundler® Stainless Steel Cable Ties

- **Extremely durable, vinyl jacketed Stainless Steel Cable Tie.**
- Smooth vinyl jacketing prevents damage to installation cable insulation.
- Stainless steel crimp sleeve for easy field installation with electrician linesman pliers, or wire cutters.
- UV protected vinyl jacket is excellent for solar installation where product durability is required.
- Use standard wire cutters to both crimp the sleeve and cut the excess wire.
- Constructed from Commercial Aircraft Grade Stainless wire with UV protected vinyl jacket.
- Not for use in a marine salt water environment. Contact Heyco for alternative materials

PART SPECIFICATIONS				PART NO.	DESCRIPTION	PART DIMENSIONS			
Minimum Tensile Strength		Maximum Bundle Diameter				A Length	B Diameter		in.
Lbs.	N	in.	mm.		in.	mm.			
100	440	2.30	58,4	<b>S6408</b>	SunBundler® 8	8	203	.06	1,6
		2.92	74,2	<b>S6410</b>	SunBundler® 10	10	254		
		3.88	98,6	<b>S6412</b>	SunBundler® 12	12	305		
		4.20	106,7	<b>S6414</b>	SunBundler® 14	14	356		
		6.36	161,5	<b>S6420</b>	SunBundler® 20	20	508		

\*Black vinyl jacketed 302/304 stainless steel wire.



**Material**

Commercial Aircraft Grade 302/304 stainless wire w/UV protected vinyl jacket and 304 stainless steel crimp sleeve




## Heyco® SunWrap™ - Heavy Duty Cable Guard



- **Easy to use: Just twist on wire!**
- Designed to shield heavier cables and cable bundles; **extend cable life.**
- Available in a **variety of sizes** that fit cable and cable bundles from 3/4" to 6" in diameter.
- **Smooth finished interior wall.**
- **Highly flexible** for ease of movement.
- Packaged as one continuous piece in a box, not spooled.
- May be **cut to desired length**, please consult Heyco.

BUNDLE RANGE				PART NO.	DESCRIPTION	PART DIMENSIONS					
Minimum Diameter		Maximum Diameter				Black	A Outside Dia.		B Pitch		C Thickness
in.	mm.	in.	mm.		in.	mm.	in.	mm.	in.	mm.	
.750	19,1	1.500	38,1	<b>8964</b>	CWG 99 PE	.93	23,6	.95	24,1	.12	3,0
1.000	25,4	2.000	50,8	<b>8966</b>	CWG 126 PE	1.12	28,4	1.25	31,8	.13	3,3
1.250	31,8	2.500	63,5	<b>8968</b>	CWG 153 PE	1.37	34,8	1.35	34,3	.14	3,5
1.500	38,1	3.000	76,2	<b>8970</b>	CWG 181 PE	1.62	41,1	1.50	38,1	.15	3,9
2.000	50,8	3.500	88,9	<b>8972</b>	CWG 234 PE	2.09	53,1	1.60	40,6	.17	4,3
3.500	88,9	6.000	152,4	<b>8974</b>	CWG 401 PE	3.50	88,9	1.95	49,5	.25	6,4

\*Standard color black or color coded



**Material**  
**Temperature Range**

High Density Polyethylene  
0°F (-18°C) to 165°F (74°C)

Quick  
Specs