

Login

Search...
Advanced Search

Visit our Other sites: FTZ | ILSCO Extrusion

Help



Home

- [About Us](#)
- [Products](#)
- [Reference](#)
- [ILSCO Product Catalog](#)

CSWD 2 HOLE SHORT W/SIGHT

Home > ILSCO Product Catalog > Compression > New Copper Compression > CSWD 2 HOLE SHORT W/SIGHT



- Manufactured from high strength seamless copper tubing.
- Electro-Tin plated.
- Maximum conductivity and excellent crimping characteristics.
- Standard barrel length with chamfered entry.
- Sight hole and chamfered barrel for visual inspection of proper cable insertion.
- Color Coded.
- UL 486A/B 90° C Listed and CSA Certified for 600 Volts.
- 1/0 AWG - 8 AWG UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
- Copper - Class B concentric, Class B compressed, Class C concentric.
- IlSCO connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools.
- Refer to Tool and Die Charts under reference tab.
- UL File E6207

Items Per Page

Compare

Bolt/Stud Size

Conductor Size

Mounting Hole Spacing

Compare	Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor Range	Bolt/Stud Size	Mounting Hole Diameter	Mounting Hole Spacing	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Ct
<input type="checkbox"/>	CSWD-250-58-1	250 kcmil	4/0 FLEX	250 kcmil - 1/0 AWG	5/8	0.656	1	2.5000	1.0880	1.0630	1.1250	4.0940	YEL
<input type="checkbox"/>	CSWD-250-12-2	250 kcmil	4/0 FLEX	250 kcmil - 1/0 AWG	1/2	.5620	2	3.100	1.0880	1.0630	1.1250	4.6940	YEL
<input type="checkbox"/>	CSWD-8-10-12	#8 AWG	#8 FLEX		10	0.219	1/2	1.2500	0.3740	0.5000	0.5620	1.9450	R
<input type="checkbox"/>	CSWD-8-10-58	#8 AWG	#8 FLEX		10	0.219	5/8	1.2500	0.3740	0.5000	0.5620	1.9450	R
<input type="checkbox"/>	CSWD-8-10-1116	#8 AWG	#8 FLEX		10	0.219	11/16	1.2500	0.3740	0.5000	0.5620	1.9450	R
<input type="checkbox"/>	CSWD-8-10-34	#8 AWG	#8 FLEX		10	0.219	3/4	1.4370	0.3740	0.5000	0.5620	2.1320	R
<input type="checkbox"/>	CSWD-8-10-1	#8 AWG	#8 FLEX		10	0.219	1	1.6870	0.3740	0.5000	0.5620	2.3820	R
<input type="checkbox"/>	CSWD-8-14-12	#8 AWG	#8 FLEX		1/4	0.281	1/2	1.2500	0.3740	0.5000	0.5620	1.9450	R
<input type="checkbox"/>	CSWD-8-14-58	#8 AWG	#8 FLEX		1/4	0.281	5/8	1.4370	0.3740	0.5000	0.5620	2.1320	R
<input type="checkbox"/>	CSWD-8-14-34	#8 AWG	#8 FLEX		1/4	0.281	3/4	1.4370	0.3740	0.5000	0.5620	2.1320	R
<input type="checkbox"/>	CSWD-8-14-1	#8 AWG	#8 FLEX		1/4	0.281	1	1.6870	0.3740	0.5000	0.5620	2.3820	R
<input type="checkbox"/>	CSWD-8-516-58	#8 AWG	#8 FLEX		5/16	0.343	5/8	1.4370	0.3740	0.5000	0.5620	2.1320	R
<input type="checkbox"/>	CSWD-8-516-34	#8 AWG	#8 FLEX		5/16	0.343	3/4	1.6870	0.3740	0.5000	0.5620	2.3820	R
<input type="checkbox"/>	CSWD-8-516-78	#8 AWG	#8 FLEX		5/16	0.343	7/8	1.6870	0.3740	0.5000	0.5620	2.3820	R
<input type="checkbox"/>	CSWD-8-516-1	#8 AWG	#8 FLEX		5/16	0.343	1	1.9370	0.3740	0.5000	0.5620	2.6320	R
<input type="checkbox"/>	CSWD-8-516-134	#8 AWG	#8 FLEX		5/16	0.343	1-3/4	2.5000	0.3740	0.5000	0.5620	3.1950	R
<input type="checkbox"/>	CSWD-8-38-34	#8 AWG	#8 FLEX		3/8	0.406	3/4	1.6870	0.3740	0.5000	0.5620	2.3820	R
<input type="checkbox"/>	CSWD-8-38-78	#8 AWG	#8 FLEX		3/8	0.406	7/8	1.9370	0.3740	0.5000	0.5620	2.6320	R
<input type="checkbox"/>	CSWD-8-38-1	#8 AWG	#8 FLEX		3/8	0.406	1	1.9370	0.3740	0.5000	0.5620	2.6320	R
<input type="checkbox"/>	CSWD-8-38-116	#8 AWG	#8 FLEX		3/8	0.406	1-1/16	1.9370	0.3740	0.5000	0.5620	2.6320	R

[Contact Us](#) [Privacy Policy](#) [Terms And Conditions](#)

©1991-2013 [CDI Technology](#) All Rights Reserved

ILSCO
4730 MADISON ROAD
CINCINNATI, OH 45227
513-533-6200
800-776-9775