



Parallel Tap Connectors - Dual Rated



TYPE GTA

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- UL Listed and CSA Certified for 600 volts
- Compact design
- Range taking
- Re-usable
- Lay-in main conductor
- Insulating cover available

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Ensures reliability for copper or aluminum conductors
- Saves space and reduces installation time
- Permits inventories to be kept to a minimum
- Provides efficient use and flexibility in the field
- No need to break the feeder cable
- Eliminates taping




Fig. 1





Fig. 2



Catalog Number		Figure Number	Wire Range		Dimensions			Hex Size		Temperature Rating
Connector	Cover		Main	Tap	L	W	H	Main	Tap	
GTA-2-2	GTC-2	1	2-12 Str.	2-12 AL 2-14 CU	1-1/4	9/16	1	Slot	Slot	90° C
GTA-0-0	GTC-0	1	1/0-2	1/0-12 AL 1/0-14 CU	1-9/16	3/4	1-1/8	Slot	Slot	90° C
GTA-250-0	GTC-250-350	1	250MCM-1/0	1/0-12 AL 1/0-14 CU	2	15/16	1-7/16	5/16	Slot	90° C
GTA-250-250	GTC-250-350	1	250MCM-1/0	250MCM-6	2-1/8	15/16	1-7/16	5/16	5/16	90° C
GTA-350-350	GTC-250-350	1	350MCM-4/0	350MCM-6	2-7/16	1	1-11/16	3/8	3/8	90° C
GTA-500-500	GTC-500	1	500MCM-350MCM	500MCM-2	2-15/16	1-1/4	2	3/8	3/8	90° C
GTA-750-500	GTC-750-500	1	750MCM-500MCM	500MCM-2	3-3/8	1-5/16	2-7/16	3/8	3/8	90° C
GTA-750-750	GTPC-750-750	2	750MCM-500MCM	750MCM-1/0	3-3/8	2-5/8	2-7/16	1/2	1/2	90° C
GTA-1000-500	Not Available	1	1000MCM-750MCM	500MCM-2	3-3/8	1-15/16	2-7/16	1/2	3/8	90° C

Insulating covers are available for most connector sizes. All covers accommodate many wire combinations and are available at a fraction of the cost of taping by hand.
 Note: If ordering with cover, add suffix w/c to catalog number.
 DE-OX Inhibitor is recommended for all aluminum terminations.

B