

Applications

- For use in wet locations to couple two ends of EMT conduit
- RACO® Raintight Steel EMT Compression Fittings have been designed to comply with the new U.L. Raintight test requirements and to comply with the requirements of the 2008 NEC 358.42 and 314.15

Product Features


- All steel construction insures mechanical protection for the raceway
- Fittings are available in 1/2" to 4" trade sizes
- Zinc electroplate finish
- All fittings are marked "Wet Locations". Allows inspecting authorities to immediately determine that the installation is up to code
- No need to disassemble the fitting prior to installation. RACO Raintight Steel EMT Compression Fittings are designed so that when they come out of the carton they can be installed directly on the conduit. No need to waste time loosening compression nuts
- No need for special tools to install properly. Install these fittings like any other Steel EMT Compression Fitting. No need for a torque wrench to insure proper installation

Compliances

- cUL_{us} - Standard 514B
- C22.2 # 18



Couplings
Steel



ORDERING INFORMATION - DIMENSIONS

COMPRESSION FITTINGS - COUPLINGS

CATALOG NUMBER	TRADE SIZE	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
2922RT	1/2"	50	250	—
2923RT	3/4"	25	125	—
2924RT	1"	15	75	—
2925RT	1-1/4"	—	20	—
2926RT	1-1/2"	—	10	—
2928RT	2"	—	10	—
2950RT	2-1/2"	—	1	—
2952RT	3"	—	1	—
2954RT	3-1/2"	—	1	—
2956RT	4"	—	1	—

DIMENSIONS

CATALOG NUMBER	A	B
2922RT	2.00	1.16
2923RT	2.15	1.38
2924RT	2.32	1.64
2925RT	2.50	2.04
2926RT	2.78	2.27
2928RT	2.88	2.74
2950RT	3.87	3.62
2952RT	4.00	4.25
2954RT	4.68	4.68
2956RT	4.93	5.18