

## TYPE T4A4

### Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- Chamfered wire entry
- UL Listed and CSA Certified for 600 volts, 90° C

### Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- Ensures reliability for copper or aluminum conductors




Fig. 1



Fig. 2

Catalog Number	Figure Number	Wire Range	Bolt Size	Dimensions									Hex Size
				C	E	F	G	H	J	K	R	T	
T4A4-250N	1	250kcmil-6	1/2	9/16	3	4	5/8	3-49/64	1-3/4	5/16	1-3/16	1-17/32	5/16
T4A4-350N	1	350kcmil-6	1/2	9/16	3	4-5/16	5/8	4-1/64	1-3/4	5/16	1-3/8	1-17/32	5/16
T4A4-600N	2	600kcmil-2	1/2	9/16	3	5-5/8	9/16	5	1-3/4	7/16	1-11/16	1-7/8	3/8
T4A4-800N	2	800kcmil-350kcmil	1/2	9/16	3-7/16	6-3/16	5/8	6	1-3/4	9/16	1-7/8	2-13/64	3/8

DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A-486B, UL File E6207

C