

Control Power Transformer, PRI 208/230/460v, SEC 115v,



Figure similar

product brandname	Control Power Transformer
Product designation	MT
Special product feature	Robust design

General technical data	
Weight [lb]	11.3 lb
Height x Width x Depth [in]	4.47 × 4.5 × 4.78 in
Ambient temperature [°F] during operation	-4 ... +104 °F
Ambient temperature during operation	-20 ... +40 °C
Country of origin	Mexico
Operating apparent output rated value	250 V·A

Enclosure	
Design of the housing	Open

Mounting/wiring	
Mounting position	Any
Mounting type	Surface mounting
Type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)

Type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
---	----------------------------------

### Inputs/ Outputs

Input dimensions of primary voltage	208/230/460vac
Output dimensions of secondary voltage	115vac
Phase number of the inputs	1
Electrical input frequency	50 ... 60 Hz
Input voltage _1	208 V
Input voltage _2	230 V
Input voltage _3	460 V
Phase number of the outputs	1
Electrical output frequency	60 ... 50 Hz
Output voltage _1 rated value	115 V

### Certificates/approvals

Certificate of suitability	UL / CSA
----------------------------	----------

### Further information

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0250G>

last modified:

06/12/2017 