


6P6C EZ RJ-11 Voice Module

PRODUCT SPECIFICATION

Package includes:

- A. 6P6C EZ RJ-11 Voice Module, 1 pc
- B. Wire Cap, 1 pc



Features and Benefits:

- Designed for all voice connectivity applications.
- Lead frame technology provides maximum performance and uninterrupted signal integrity.
- Engineered to provide 110 IDC termination reducing installation time.
- One piece termination cap allows for a quick and easy termination.
- Includes an integrated USOC/UTP color wiring diagram.
- Compatible with all IC107 faceplates, inserts, surface mount boxes, and blank patch panels.
- Compatible with all IC108 furniture faceplates, bezels, and surface mount boxes.
- Used with ICC ICLC2, ICLC4, ICLC6 line cords and 110 punch down tool ICACSPDT00.
- Available in almond, black, blue, gray, green, ivory, orange, purple, red, white, and yellow.
- UL listed.






MODULE, VOICE, RJ-11, EZ

ITEM NO.	IC1076V0XX
DWG NO.	PS1076V000

REV.	F
PAGE NO.	1



CUSTOMER CARE / TECHNICAL SUPPORT * CSR@ICC.COM / 888-ASK-4-ICC (275-4422) *14700 Alondra Blvd., La Mirada, CA 90638 * www.icc.com



USOC WIRING

6	BLUE
5	YELLOW
4	GREEN
3	RED
2	BLACK
1	WHITE

UTP WIRING

6	GREEN
5	ORANGE
4	WHITE/BLUE
3	BLUE
2	WHITE/ORANGE
1	WHITE/GREEN

NOTE: UNLESS OTHERWISE SPECIFIED

1. RJ-11 VOICE MODULE:

A. ELECTRICAL:

- CURRENT RATING: 1.5 AMPS MAX
- VOLTAGE RATING: 150 VOLTS ALTERNATING
- DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS, 60 HZ
- INSULATION RESISTANCE: > 10 MOHMS

B. MECHANICAL:

- MATED FORCE: 5 LBS MAX
- UNMATED FORCE: 5 LBS MAX
- PLUG RETENTION FORCE: 20 LBS MIN
- DURABILITY: 750 CYCLES

C. PHYSICALS:


- HOUSING: HIGH IMPACT, FLAME RETARDANT PLASTIC, UL 94V-0
- CONTACT: PHOSPHOR BRONZE GOLD PLATING OVER 100 INCHES OF NICKEL
- GOLD PLATING: 1.27 MICRON/50 MICRO INCH MIN
- CONNECTOR: INSULATION DISPLACEMENT CONNECTOR (IDC)
ACCEPTS 22~24 AWG SOLID WIRE

D. COLORS: XX: AL-ALMOND, BK-BLACK, BL-BLUE, GN-GREEN, GY-GRAY, IV-IVORY, OR-ORANGE, PR-PURPLE, RD-RED, WH-WHITE, & YL-YELLOW



NEXT: (NEAR END CROSS TALK)	1 MHz > 65 dB
	10 MHz > 50 dB
	16 MHz > 46 dB
	20 MHz > 44 dB
INSERTION LOSS:	10 MHz > 0.008 dB
	16 MHz > 0.02 dB

UL US FILE NO. 125268

MODULE, VOICE, RJ-11, EZ		 Premium Products Proven Performance Competitive Prices	
ITEM NO.	IC1076V0XX		REV. F
DWG NO.	PS1076V000	PAGE NO.	2

CUSTOMER CARE / TECHNICAL SUPPORT * CSR@ICC.COM / 888-ASK-4-ICC (275-4422) *14700 Alondra Blvd., La Mirada, CA 90638 * www.icc.com