






## Nylon Fully-Insulated Female Disconnects

Wire Range	Tab Size In.	Max. Wire Ins. Dia. In.	Qty.	Cat. No.	Qty.	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> ) 	.250 x .032 (6.35mm x 0.8mm)	0.15 (3.8mm)	25	<b>83-9771</b>	1,000	<b>84-9771</b>
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	.250 x .032 (6.35mm x 0.8mm)	0.185 (4.7mm)	25	<b>83-9781</b>	1,000	<b>84-9781</b>
12 – 10 AWG (4,0-6,0mm <sup>2</sup> ) 	.250 x .032 (6.35mm x 0.8mm)	0.244 (6.2mm)	25	<b>83-9791</b>	500	<b>84-9791</b>


105° C/300 Volts max.

## Vinyl Fully-Insulated Receptacle Disconnects

Wire Range	Max. Wire Ins. Dia. In.	Quantity	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> ) 	0.150 (3.8mm)	25	<b>83-8101</b>
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	0.185 (4.7mm)	25	<b>83-8111</b>

75° C/300 Volts max.

## Non-Insulated Flag Female Disconnect\*

Wire Range	Tab Size In.	Quantity	Cat. No.
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	.250 x .032 (6.35 x 0.8mm)	25	<b>83-9401</b>

105° C/300 Volts max.

## Disconnect Adapter - Male to Female (2-1)\*

Tab Size (In.)	Quantity	Cat. No.
.250 x .032 (6.35mm x 0.8mm) 	25	<b>83-9801</b>

105° C/300 Volts max.

## Non-Insulated Parallel Splices\*

Wire Range	Qty.	Cat. No.	Qty.	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> )	25	<b>83-9071</b>	—	—
16 – 14 AWG (1,5-2,5mm <sup>2</sup> )	25	<b>83-9081</b>	1,000	<b>84-9081</b>
12 – 10 (4,0-6,0mm <sup>2</sup> )	25	<b>83-9091</b>	1,000	<b>84-9091</b>

105° C/600 Volts max.

\*Not UL Listed

1-800-435-0705 CUSTOMER ASSISTANCE




## Non-Insulated Butt Splices\*



Wire Range	Qty.	Cat. No.	Qty.	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> )	25	<b>83-9001</b>	—	—
16 – 14 AWG (1,5-2,5mm <sup>2</sup> )	25	<b>83-9011</b>	1,000	<b>84-9011</b>
12 – 10 (4,0-6,0mm <sup>2</sup> )	25	<b>83-9021</b>	500	<b>84-9021</b>
8 (8,0mm <sup>2</sup> )	25	<b>83-9031</b>	250	<b>84-9031</b>
6 (14,0mm <sup>2</sup> )	20	<b>83-9041</b>	—	—
4 (22,0mm <sup>2</sup> )	20	<b>83-9051</b>	—	—




105° C/600 Volts max.

## Vinyl Insulated Butt Splices

Wire Range	Max. Wire Ins. Dia. In.	Qty.	Cat. No.	Qty.	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> ) 	.157 (4.0mm)	25	<b>83-9281</b>	1,000	<b>84-9281</b>
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	.177 (4.5mm)	25	<b>83-9291</b>	1,000	<b>84-9291</b>
12 – 10 (4,0-6,0mm <sup>2</sup> ) 	.248 (6.3mm)	25	<b>83-9301</b>	500	<b>84-9301</b>




75° C/600 Volts max.

## Vinyl Insulated Parallel Splices

Wire Range	Max. Wire Ins. Dia. In.	Qty.	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> ) 	.157 (4.0mm)	1,000	<b>83-9351</b>
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	.177 (4.5mm)	1,000	<b>83-9361</b>
12 – 10 (4,0-6,0mm <sup>2</sup> ) 	.248 (6.3mm)	500	<b>83-9371</b>

75° C/600 Volts max.

## Tap Splice Connectors

Wire Range	Color	Quantity	Cat. No.
22 – 18 AWG (0,5-1,0mm <sup>2</sup> ) 	Red	25	<b>83-3261</b>
16 – 14 AWG (1,5-2,5mm <sup>2</sup> ) 	Blue	25	<b>83-3271</b>
12 – 10 (4,0-6,0mm <sup>2</sup> ) 	Yellow	25	<b>83-3281</b>

75° C/600 Volts max.



WWW.IDEALINDUSTRIES.COM