

Byb3RIY3RvcnMtcG93ZXItc3RyaXBzL3Bvd2VyLXN0cmlwcy5hc3B4ZBYCZg8WAh8ABQxQb3dlciBTdHJpcHNkAgMPDxYCHwQFMC9zdXJnZS1wcm90ZWNI



designed to be better.

Search

Weather-Resistant GFCI Receptacle, Light Almond

1595TRWRLA

GFCI Receptacle Tamper-Resistant/Weather-Resistant, 10kA SCCR, 15A 120V, Light Almond


Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0 Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS

Weather-Resistant GFCI Receptacle, White

Weather-Resistant GFCI Receptacle, Brown

Weather-Resistant GFCI Receptacle, Gray





Weather-Resistant GFCI Receptacle, Ivory

- SPECIFICATIONS
- RESOURCES

features & benefits

- Designed for extra durability and a long service life when installed in harsh environments: outdoor, garages, workshops, wash down areas, commercial kitchens, and labs.
- Weather-Resistant: Meets 2008 National Electrical Code® Weather-Resistant requirements.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: Ultraviolet light exposure test Cold impact test Accelerated aging test Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- Dust- and insect-resistant.
- Rubber curtains let plug blades in; keep dust, water and insects out.
- Integral gasket seals receptacle, protecting critical electronic components.
- Exceeds UL corrosion requirements – survives 4X the required corrosion test cycles.
- Safelock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long nickel post-plated steel mounting strap.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [Tamper-Resistant Receptacles \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)

 [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)

specifications

General Info

- Color: Light Almond
- Product Series: TradeMaster
- Type: GFCI Receptacle
- Special Features: Weather-Resistant
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614

Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information




- Amps: 15 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance




- Country of Origin: CHINA
- Buy American Act Status: No
-

resources

BROCHURE

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [Tamper-Resistant ReceptaclesPDF \(791.69kb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)