

TYPE SGB

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- Lay-in feature
- Stainless steel hardware
- Serrations in conductor wire way
- Unique clamp design
- 1/4" max frame thickness
- Meets ASTM B117-09

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- For corrosion resistance, greater torque and ease of installation
- Cuts oxidation
- No mounting hardware required, reusable
- Mount to solar panel frames
- Resistance to outdoor salt spray





Fig. 1



Fig. 2



C

| Catalog Number | Figure Number | Ground Wire Range | Dimensions | | |
|----------------|---------------|-------------------|------------|------|-------|
| | | | L | W | H |
| SGB-4 | 1 | 4-14 | 1.375 | .500 | .940 |
| SGB-5 | 2 | 4-14 | 1.375 | .500 | 1.440 |

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
 UL 467 for grounding and bonding. UL File E34440
 UL2703 Recognized E354420 Vol. 1
 DE-OX Inhibitor is recommended for all aluminum terminations.