

TYPE GTA

B

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- UL Listed and CSA Certified for 600 volts, Temp. rating 90° C
- Compact design
- Range taking
- Re-usable
- Lay-in main conductor
- Insulating cover available

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Ensures reliability for copper or aluminum conductors
- Saves space and reduces installation time
- Permits inventories to be kept to a minimum
- Provides efficient use and flexibility in the field
- No need to break the feeder cable
- Eliminates taping




Fig. 1



Fig. 2



Catalog Number		Figure Number	Wire Range		Dimensions			Hex Size	
Connector	Cover		Main	Tap	L	W	H	Main	Tap
GTA-2-2	GTC-2	1	2-12 str	2-12 AL 2-14 CU	1-1/4	9/16	1	Slot	Slot
GTA-0-0	GTC-0	1	1/0-2	1/0-12 AL 1/0-14 CU	1-9/16	3/4	1-1/8	Slot	Slot
GTA-250-0	GTC-250-350	1	250kcmil-1/0	1/0-12 AL 1/0-14 CU	2	15/16	1-7/16	5/16	Slot
GTA-250-250	GTC-250-350	1	250kcmil-1/0	250kcmil-6	2-1/8	15/16	1-7/16	5/16	5/16
GTA-350-350	GTC-250-350	1	350kcmil-4/0	350kcmil-6	2-7/16	1	1-11/16	3/8	3/8
GTA-500-500	GTC-500	1	500kcmil-350kcmil	500kcmil-2	2-15/16	1-1/4	2	3/8	3/8
GTA-750-500	GTC-750-500	1	750kcmil-500kcmil	500kcmil-2	3-3/8	1-5/16	2-7/16	3/8	3/8
GTA-750-750	GTPC-750-750	2	750kcmil-500kcmil	750kcmil-1/0	3-3/8	2-5/8	2-7/16	1/2	1/2
GTA-1000-500	Not Available	1	1000kcmil-750kcmil	500kcmil-2	3-3/8	1-15/16	2-7/16	1/2	3/8

Insulating covers are available for most connector sizes. All covers accommodate many wire combinations and are available at a fraction of the cost of taping by hand.

Note: If ordering with cover, add suffix w/c to catalog number.

DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A-486B, UL File E6207