

AAUdRmFjaWxpdHkgTWFuYWdlbWVudCBTb2x1dGlbnNkAgYPZBYCAgEPDxYCHwQFGy9jb21tZXJjaWFsL2hiYWx0aGNhcmUuYXNweGQWAmYYPFglfAA



designed to be better.

Search

Heavy-Duty Hospital Grade Compact Design Receptacle, Back & Side Wire, 20A, 125V, Gray

8300HGRY

Heavy-Duty Hospital Grade Compact Design Duplex Receptacle, Back & Side Wire, 20amp 125volt, Gray

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, White



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Brown



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Black



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Ivory



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Light Almond



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Auto-ground clip assures positive ground.
- Compact design for easy installation.
- Tri-drive terminal and mounting screws.

Top 5 Resources

- [HG Heavy Duty Compact Design Receptacles, SF706R1 \(Cutsheet\)](#)

specifications

General Info

- Color: gray
- Type: Compact Design,Receptacles
- Duty: Heavy Duty
- Special Features: Back,Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .780"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

CUTSHEET

- [HG Heavy Duty Compact Design Receptacles, SF706R1PDF \(151.55kb\)](#)