



designed to be better.

20 Amp NEMA Connector L620 - Black Back, White Front Body

L620C

Turnlok Connector 3wire 20amp 250v

Where to buy

0





Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2 (Cutsheet)

specifications

General Info

- Color: Black, White
- Type: Connector
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Diameter U S: 2.20"
- Length: 3.33"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L620
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2PDF (309.83kb)