

ILSCO Aluminum Panelboard Lugs - Dual Rated



TYPE PB



Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro-tin plated
- Chamfered wire entry
- UL Listed and CSA Certified for 600 volts, 90° C
- Stacked design

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- Ensures reliability for copper or aluminum conductors
- Saves space and reduces installation time

C



Catalog Number	Figure Number	Wire Range	Bolt Size	Dimensions									Hex Size
				C	E	F	G	H	J	K	R	T	
PB2-300	1	300kcmil-6	5/16	21/64	1	3	15/32	1	-	5/16	2	2-5/16	5/16
PB2-500	2	500kcmil-4/0	1/4	9/32	1-11/16	2-29/32	1/4	1-7/16	11/16	5/8	2-3/8	1-27/64	3/8
PB2-600	4	600kcmil-2	3/8	13/32	2-11/32	4-29/32	3/8	1-1/2	1-3/8	3/4	3	3-29/64	1/2
PB3-600	6	600kcmil-2	3/8	13/32	2-11/32	4-29/32	3/8	2-15/32	1-3/8	3/4	3	3-29/64	1/2
PB4-600	8	600kcmil-2	3/8	13/32	2-11/32	4-29/32	3/8	2-15/32	1-3/8	3/4	3	3-29/64	1/2
PB2-750	4	750kcmil-1/0	3/8	13/32	2-11/32	4-29/32	3/8	1-11/16	1-3/8	3/4	3	3-29/64	1/2
PB4-750	8	750kcmil-1/0	3/8	13/32	2-11/32	4-29/32	3/8	2-5/8	1-3/8	3/4	3	3-29/64	1/2
PB3-600-2N	5	600kcmil-2	1/2	9/16	3-1/8	5-11/16	3/8	2-15/32	1-3/4	3/4	3	3-29/64	1/2
PB2-600-2N	3	600kcmil-2	1/2	9/16	3-1/8	5-11/16	3/8	1-1/2	1-3/4	3/4	3	3-29/64	1/2
PB2-750-2N	3	750kcmil-1/0	1/2	9/16	3-1/8	5-11/16	3/8	1-11/16	1-3/4	3/4	3	3-29/64	1/2
PB4-600-2N	7	600kcmil-2	1/2	9/16	3-1/8	5-11/16	3/8	2-15/32	1-3/4	3/4	3	3-29/64	1/2
PB4-750-2N	7	750kcmil-1/0	1/2	9/16	3-1/8	5-11/16	3/8	3-1/16	1-3/4	3/4	3	3-29/64	1/2

DE-OX Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A-486B, UL File E6207

