



Aluminum Mechanical Lugs - Dual Rated Three Conductor



TYPE T3A

Features

- Manufactured from high strength 6061-T6 aluminum alloy
- Electro tin plated
- Chamfered wire entry
- UL Listed and CSA Certified for 600 volts

Benefits

- Suitable for use with either copper or aluminum conductors
- Provides low contact resistance
- Provides ease of installation
- Ensures reliability for copper or aluminum conductors

C




Fig. 1



Fig. 2



Fig. 3



Fig. 4

Catalog Number	Figure Number	Wire Range	Bolt Size	Dimensions									Hex Size	Temperature Rating
				C	E	F	G	H	J	K	R	T		
T3A2-2	1	Three: 2-14	5/16	11/32	1-11/16	2-3/16	11/32	1-19/32	7/8	3/16	5/8	13/16	Slot	90° C
T3A2-0	1	Three: 1/0-14	3/8	7/16	2-5/32	2-29/32	11/32	1-15/16	1	1/4	7/8	15/16	Slot	90° C
T3A2-3/0N	1	Three: 3/0-6	1/2	9/16	3	3-7/8	5/8	2-13/16	1-3/4	5/16	1-1/8	1-1/2	5/16	90° C
T3A2-250N	1	Three: 250MCM-6	1/2	9/16	3	4	5/8	2-13/16	1-3/4	5/16	1-3/16	1-17/32	5/16	90° C
T3A2-350N	1	Three: 350MCM-6	1/2	9/16	3	4-5/16	5/8	3	1-3/4	5/16	1-3/8	1-17/32	5/16	90° C
T3A2-600N	2	Three: 600MCM-2	1/2	9/16	3	5-5/8	9/16	3-3/4	1-3/4	7/16	1-11/16	1-49/64	3/8	90° C
T3A2-800N	2	Three: 800MCM-350MCM	1/2	9/16	3-7/16	6-3/16	5/8	4-1/4	1-3/4	9/16	1-7/8	2-21/64	1/2	90° C
T3A2-1000N	2	Three: 1000MCM-500MCM	1/2	9/16	3-7/16	6-3/16	5/8	4-3/4	1-3/4	9/16	1-7/8	2-21/64	9/16	90° C
T3A4-2	3	Three: 2-14	5/16	11/32	1-11/16	2-3/16	11/32	1-19/32	7/8	3/16	5/8	13/16	Slot	90° C
T3A4-0	3	Three: 1/0-14	3/8	7/16	2-5/32	2-29/32	11/32	1-15/16	1	1/4	7/8	15/16	Slot	90° C
T3A4-3/0N	3	Three: 3/0-6	1/2	9/16	3	3-7/8	5/8	2-13/16	1-3/4	5/16	1-1/8	1-1/2	5/16	90° C
T3A4-250N	3	Three: 250MCM-6	1/2	9/16	3	4	5/8	2-13/16	1-3/4	5/16	1-3/16	1-17/32	5/16	90° C
T3A4-350N	3	Three: 350MCM-6	1/2	9/16	3	4-5/16	5/8	3	1-3/4	5/16	1-3/8	1-17/32	5/16	90° C
T3A4-600N	4	Three: 600MCM-2	1/2	9/16	3	5-5/8	9/16	3-3/4	1-3/4	7/16	1-11/16	1-49/64	3/8	90° C
T3A4-800N	4	Three: 800MCM-350MCM	1/2	9/16	3-7/16	6-3/16	5/8	4-1/4	1-3/4	9/16	1-7/8	2-21/64	1/2	90° C
T3A4-1000N	4	Three: 1000MCM-500MCM	1/2	9/16	3-7/16	6-3/16	5/8	4-3/4	1-3/4	9/16	1-7/8	2-21/64	9/16	90° C

DE-OX Inhibitor is recommended for all aluminum terminations.