Atra TOUGH Meet Intermatic Die Cast Lineup

WP3110MXD Single Gang



WP1250MXD
Double Gang



WP1030MXD Double Gang



WP1250MVXD
Single Gang



WP1010MXD Single Gang



WP1010HMXD Single Gang



Model	Туре	Depth	Flexi-Guard Inserts	UPC	Length	Width	Height
WP3110MXD	Single-Gang	2 3/4	WP17	078275130098	6.375	3.875	2.875
WP1030MXD	Double-Gang	3 1/8	WP217	078275130142	6.312	5.75	3.25
WP1010MXD	Single-Gang	3 1/8	WP17	078275130135	6.375	3.875	3.25
WP1250MXD	Double-Gang	4 5/8	WP217	078275130111	6.312	5.75	4.75
WP1250MVXD	Single-Gang / Vertical	4 5/8	WP17	078275130104	6.375	3.875	4.75
WP1010HMXD	Single-Gang / Horizontal	3 1/8	WP17	078275130128	4.375	5.75	3.25

Meets/Exceeds all 2011 NEC Requirements for Extra-Duty Application and Wet Locations








Meets/Exceeds all 2011 NEC Requirements for Extra-Duty Application and Wet Locations

NOTED AND THE



(For durability and longevity)-

Impact Rated

(Withstands today's destructive forces)

Reinforced Hinge (40 lb stress test)

> NEMA 3R Enclosure rating

Recommended for 14 gauge or lighter cord sets

Lockable Hasp

(Accepts up to .285 in dia shank)

Sleek Industrial Design

Easy to Open (Use thumb & push to the right)

All Die Cast Units come with Flexi-Guard Inserts



Single Gang WP-WP17



Double Gang WP-WP217



INTERMATIC*
www.intermatic.com