



Pass & Seymour

Wall Plates Stainless Steel One & Two Gang

SS1, SS2, SS8, SS82, SS26, SS262, SS13, SS23, SS7, SS72, SS720

Our most corrosion-resistant metal wall plates.


These brushed-finish wall plates are made with .032" Type 302 stainless steel. This alloy is nonmagnetic and contains 18 percent chromium and 8 percent nickel for superior corrosion resistance. As a result, these plates will endure in corrosive atmospheres — and withstand abuse in any commercial application.



Features & Benefits

Constructed of .032 inch thick Type 302 brushed stainless steel.

Aesthetically pleasing contour design.



Packaged in protective film, with finish-matching screws.

SS262, SS13












Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

SF2502R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

Wall Plates Stainless Steel One & Two Gang

Ordering Information

Description	Catalog Number	Description	Catalog Number
Stainless Steel Toggle Switch Openings			
One Gang 	SS1	Two Gang 	SS2
Stainless Steel Duplex Receptacle Openings			
One Gang 	SS8	Two Gang 	SS82
Stainless Steel Decorator Openings			
One Gang 	SS26	Two Gang 	SS262
Stainless Steel Blank Plates — Box Mounted			
One Gang 	SS13	Two Gang 	SS23
Stainless Steel Single Receptacle Openings			
One Gang 	SS7	Two Gang 	SS72
Stainless Steel Power Outlet Receptacle Opening			
One Gang 	SS720		

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Wall Plates Stainless Steel One & Two Gang



Technical Specifications


3rd Party Compliance	
UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices. CSA Certified.	

Performance	
Environmental	Corrosion-Resistant


Materials	
Plate Material	.032" 302 Stainless Steel
Plate Finish	Brushed
Screws	302 Stainless Steel

Warranty

1 Year



Dimensions for One Gang




Dimensions for Two Gang

Complementary Devices & Accessories




WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Brass
- Aluminum
- Dustproof Stainless Steel Covers




WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers
- Boxes



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF2502R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour