


Technical Specifications Tamper-Resistant Construction Grade Single Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125V




Typical Specifications	
Manufacturer's Identification: Legrand/Pass & Seymour TR5251	
Description: Straight Blade Single Receptacle – Tamper-Resistant Construction Grade	
Type: 2 Pole, 3 Wire Grounding	
Rating: 15A, 125V	
Configuration: NEMA 5-15R	
3rd Party Compliance: UL Listed, File Number E140596, Standard UL498, Federal Specification WC596, CSA Certified, Standard CSA-C22.2 No. 42. Conforms to NEMA WD-1 and WD-6.	



Catalog Number	Color	Rating	NEMA Config. No.	Catalog Number	Color	Rating	NEMA Config. No.
□ TR5251I	Ivory	15A 125V	5-15R	□ TR5351I	Ivory	20A 125V	5-20R
□ TR5251W	White	15A 125V	5-15R	□ TR5351W	White	20A 125V	5-20R
□ TR5251	Brown	15A 125V	5-15R	□ TR5351	Brown	20A 125V	5-20R
□ TR5251LA	Lt. Al.	15A 125V	5-15R	□ TR5351LA	Lt. Al.	20A 125V	5-20R

Performance			
Electrical			
Dielectric Voltage	Withstands 2000V minimum		
Maximum Working Voltage	125V		
Current Interrupting	Certified for current interrupting at full-rated current		
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current		
Mechanical			
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)		
Terminal Accommodation	#14 – #10 AWG copper conductor only		
Product Identification	Ratings are a permanent part of the device		
Environmental			
Flammability	UL94 V2		
Materials			
Face	Nylon	Terminal Screws	Tri-Drive Brass
Back Body	PVC	Hex Head	
Contacts	.032" (.8)Brass	Grounding Screw	Tri-Drive Zinc-Plated Steel
Clamping Plate	.080" Steel	Assembly Rivets	Steel
Mounting Strap	.042" Steel	Mounting Screws	Tri-Drive Steel
Tamper-Resistant Shutters	Thermoplastic		

Consult Straight Blade Section B for complete compliance listing.



Project
Location/Type