

Strain Relief Cord Connectors

SKINDICHT® DIX Bushings

Multiple Cable Sealing Bushing for PG & Polyamide NPT SKINTOP® Cable Glands







SKINTOP® DIX is a multiple hole sealing bushing designed to allow several cables to be inserted through one cable gland. This results in a reduction of space and cost, as a separate cable gland is not required for each cable.



SKINTOP® DIX-DV Inserts

Technical Data:

 Color:	Natural
 Materials:	Silicone
 Temperature:	-40°C to +100°C
 Protection Seal:	IP 54 IP 68 when all holes are filled

Special shapes available on request. Consult factory for details.

Part Number	Thread Type & Size*	# of Holes	Size of Holes		Standard Pack Size
			inches	mm	
53607225	PG-7	2	0.098	2.5	100
53607417	PG-7	4	0.067	1.7	100
53609230	PG-9 or NPT-3/8"	2	0.118	3.0	100
53611225	PG-11	2	0.098	2.5	100
53611240	PG-11	2	0.157	4.0	100
53611330	PG-11	3	0.118	3.0	100
53611430	PG-11	4	0.118	3.0	100
53613250	PG-13 or NPT-1/2"	2	0.197	5.0	100
53613340	PG-13 or NPT-1/2"	3	0.157	4.0	100
53613440	PG-13 or NPT-1/2"	4	0.157	4.0	100
53616140	PG-16	1	0.157	2.5	50
53616225	PG-16	2	0.98	4.0	50
53616240	PG-16	2	0.157	4.0	50
53616260	PG-16	2	0.236	6.0	50
53616340	PG-16	3	0.157	4.0	50
53616350	PG-16	3	0.197	5.0	50
53616356	PG-16	3	0.220	5.6	50
53616360	PG-16	3	0.236	6.0	50
53616440	PG-16	4	0.157	4.0	50
53616450	PG-16	4	0.197	5.0	50
53616540	PG-16	5	0.157	4.0	50
53621270	PG-21or NPT-3/4"	2	0.276	7.0	50
53621280	PG-21or NPT-3/4"	2	0.315	8.0	50
53621370	PG-21or NPT-3/4"	3	0.276	7.0	50
53621380	PG-21or NPT-3/4"	3	0.315	8.0	50
53621460	PG-21or NPT-3/4"	4	0.236	6.0	50
53621550	PG-21or NPT-3/4"	5	0.197	5.0	50
53621640	PG-21or NPT-3/4"	6	0.157	4.0	50
53629290	PG-29 or NPT-1"	2	0.354	9.0	50
53629390	PG-29 or NPT-1"	3	0.354	9.0	50
53629470	PG-29 or NPT-1"	4	0.276	7.0	50
53629480	PG-29 or NPT-1"	4	0.315	8.0	50
53629490	PG-29 or NPT-1"	4	0.354	9.0	50
53629556	PG-29 or NPT-1"	5	0.220	5.6	50
53629570	PG-29 or NPT-1"	5	0.276	7.0	50
53629675	PG-29 or NPT-1"	6	.295	7.5	50
