





Pass & Seymour



Maintained and Momentary Contact



Locking

Switches Manual Controllers

15, 20 & 30A, 120/277VAC – Maintained Contact

15, 20 & 30A, 120/277VAC – Momentary Contact

Applications

For ON-OFF control of motors on small machine tools, pumps, fans and air conditioning equipment that require heavy-duty AC Double Throw Center OFF controls.

Features

- Oversized silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 – #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498 NT key.
- Normally open.

Catalog Number		Rating		Color
S.P.D.T.	D.P.D.T.	A.	VAC	
Maintained Contact Three Position – Two Circuit, Center Off				
1221I	1222I	15	120/277	Ivory White Brown Light Almond Locking
1221W	1222W	15	120/277	
1221	1222	15	120/277	
1221LA		15	120/277	
1221L	1222L	15	120/277	
1225I	1226I	20	120/277	
1225W	1226W	20	120/277	
1225	1226	20	120/277	
1225GRY		20	120/277	
1225LA		20	120/277	
1225L	1226L	20	120/277	
1227I	1228I	30	120/277	Ivory Brown
1227	1228	30	120/277	
Maintained Contact Either Direction Two Position, No Center Off				
1275	1276	30	120/277	Brown
Momentary Contact Either Direction Three Position, Center Off				
1250I		15	120/277	Ivory White Brown Gray Red Locking
1250W		15	120/277	
1250		15	120/277	
1250GRY		15	120/277	
1250RED		15	120/277	
1250L		15	120/277	
1251I		20	120/277	Ivory White Brown Gray Light Almond Locking
1251W		20	120/277	
1251		20	120/277	
1251GRY		20	120/277	
1251LA		20	120/277	
1251L		20	120/277	
	1256I	30	120/277	Ivory White Brown Locking
1255	1256W	30	120/277	
1255L	1256	30	120/277	
	1256L	30	120/277	

Catalog Number

Description

Lock Switch Replacement Keys

1498

Fits switches manufactured before 1976.

1498NT

Fits switches manufactured between 1976-present.

HP Conversion Table

1221 Series		1250 Series	
15 Amp	1/2 Horsepower at 120VAC 2 Horsepower at 240VAC	15 Amp	1/2 Horsepower at 120VAC 2 Horsepower at 240VAC
20 Amp	1 Horsepower at 120VAC 2 Horsepower at 240VAC	20 Amp	1 Horsepower at 120VAC 2 Horsepower at 240VAC
30 Amp	2 Horsepower at 120VAC 2 Horsepower at 240VAC	30 Amp	2 Horsepower at 120VAC 2 Horsepower at 240VAC

UL Listed.
CSA Certified.
All devices listed on this page conform to NEMA WD-1 and WD-6.

Switches PlugTail™ Specification Grade Decorator Switches

legrand®
Pass & Seymour

Switches

Auto-ground clip
assures positive ground.

Shallow design
for easier installation.

Heavy-gauge steel strap for superior strength.

No exposed terminals create a finger-safe application before, during, and after installation.




Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.



Polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.



WAGO push-in connectors are available to further speed up installation.

PT2626W

PlugTail™ Spec Grade Decorator Switches