

LED High Bay/Site Utility Series



Stock No.	Product Description
LED-8026-DL	GL-120/277-100-300-DL (Daylight) Utility Light
LED-8026-NW	GL-120/277-100-300-NW (Neutral White) Utility Light

Description:

Fully encapsulated, 120/277 Volt, E39 mogul base mounting that integrates energy saving LED technology into a powerful yet energy saving SMD high bay/utility lamp. Available in Daylight (DL) or Neutral White (NW).

- 100 Watts
- 120 - 277 Volt operation
- Daylight DL (5700K), Neutral White NW (3000K)
- Lumens: 8300(DL), 8200(NW)
- 300 on-board SMD LEDs
- Up to 50,000 hour lamp life
- Active Cooling Delta 70K Hr Fan
- Not Dimmable
- 5 year warranty (see www.led-llc.com for full details)
- Patented under 29/415,685
- LM79, IES Available
- UL Damp Location Listed

Applications:

LED High Bay/Site Utility Series lamps can impact energy usage and costs in a major way for communities and housing developments with minimal to no maintenance costs thanks to the up to 50,000 hour lamp life.

- Site / Roadway / Post Top
- Security lighting
- Parks and quads
- Municipal lighting
- Parking Garage
- Low Bay Applications
- Parking Garages
- Gas Station Canopy Lighting
- Warehouse High Bay

NOTE: When retrofitting LED to HID fixture, ballast must be bypassed when present. Eliminating the ballast saves additional costs related to maintenance, energy consumption and performance. Additionally, by-passing ballast will insure no RFI interference.



Packaging:

Master-pack: 4 each



Light Efficient Design

a division of TADD, LLC



Technical Specifications:

Bulb Type:	Site/Warehouse	Mounting:	E39 Mogul Base
Bulb Material:	Alum/Polycarbon	Replaces:	250W MH
UV:	None	Life Time:	Up to 50,000 Hrs.
Output Power:	100W	Input Voltage:	AC 120 - 277V
Lumens:	8300(DL) 8200(NW)	Beam Angle:	360 °
Dimensions:	7-7/8" x 8-1/8" 200mm x 207mm	Kelvin Temp:	(DL) 5700K (NW) 3000K
Lumen per Watt:	80	LEDs:	300 SMD LEDs
Power Factor:	99	Mercury:	No
CRI:	84	Dimmable:	No

Note: All specification information falls within a $\pm 2\%$ range and is subject to change without notice.

NOTE: Light Efficient Design is providing this information to the general public. Please note that all products contained herein are trademarked, copyrighted, and/or have patents pending. Any use of these designs is strictly prohibited without prior written consent. Light Efficient Design protects its proprietary information vigorously in the courts of the United States of America.

106 S. Wynstone Park Drive • N. Barrington, IL 60010
(847) 380-3540 • FAX: (847) 380-3542
www.led-llc.com