

Technical Specifications 15A Turnlok® Receptacles



Typical Specifications

Manufacturer's Identification: Legrand/Pass & Seymour 4700
 Description: Locking Receptacle, Power Supply
 Type: 2 Pole, 3 Wire Grounding
 Rating: 15A, 125V
 Configuration: NEMA L5-15R
 3rd Party Compliance: UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596. CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs. Conforms to NEMA WD-1 and WD-6.

Amps	Catalog Number	NEMA Config. No.	Amps	Catalog Number	NEMA Config. No.
15	☐ 4710	L5-15R	15	☐ 4550	L6-15R
15	☐ 4700	L5-15R	15	☐ 4760	L7-15R
15	☐ 4792	L5-15R	15	☐ 4750	L7-15R
15	☐ 4560	L5-15R			

Performance

Electrical

Dielectric Withstand Voltage 2000V minimum
 Maximum Working Voltage 600VAC
 Current Interrupting Certified for current interrupting at full-rated current
 Temperature Rise 30°C max. after 50 cycles at 150% rated current

Mechanical

Terminal Accommodation #18 AWG min. – #10 AWG max.
 Product Identification Amperage, Voltage, NEMA Configuration molded into face


Environmental

Flammability UL94 V2
 Operating Temperature Maximum continuous +75°C, minimum -40°C without impact


Materials

Front Body Nylon
 Back Body Nylon
 Mounting Strap Steel
 Contacts Brass
 Terminal Clamps Brass
 Terminal Screws Brass
 Mounting Screws Zinc-Plated Steel


Consult Turnlok® Section H for complete compliance listing.




4710




4700




4792




4560



4760



4750



4550



Project
Location/Type