

| |
|----------------|
| Catalog Number |
| Notes |
| Type |

FEATURES & SPECIFICATIONS

INTENDED USE

Recessed LED kits include housing, trim, and wire connectors in one package. The LED kit is the most economical means to create a well lit environment with exceptional energy efficiency and near zero maintenance. The LED kit maintains at least 70% light output for 35,000 hours.

CONSTRUCTION

Steel housing with 3 remodel clips and 3 wire nuts for installation in existing plaster, sheet rock or mechanical ceiling. Heavy-gauge galvanized steel raceway arm. Durable, powder coat paint prevents rust. Easily converts to new construction application using accessories (sold separately).

Galvanized steel junction box with three 7/8" knockouts with slots for pryout. Not suitable for pulling wires.

Hook & hang snap-on J-box doors for easy access.

Rated for 90° C. Ground wire provided.

Utilizes 3000K color temperature LEDs.

OPTICS

Lower white baffle splay recesses optical system into the ceiling to prevent glare and provide a traditional look.

ELECTRICAL SYSTEM

High-efficiency driver mounted on the module. Primary power disconnect provided for simple connection to a dedicated LED connector in the housing.

Dimming down to 15%. See page 2 for recommended triac dimmers.

Standard input wattage is 9.0 W, 45 lumens per watt; equivalent to 50 watt Par20.

LISTINGS


CSA certified for use in the US and Canadian safety standards. California T24 compliant. Damp location listed.

WARRANTY

Three year limited warranty covering defects in materials and workmanship, including LED and driver.

Note: Specifications subject to change without notice.

| Specifications |
|--------------------------------|
| Aperture: 4" (10.2) |
| Ceiling opening: 4-1/8" (10.5) |
| Overlap trim: 4-7/8" (12.4) |
| Height: 6" (15.2) |
| Length: 7-3/4" (19.7) |



All dimensions are inches (centimeters).

LED Recessed Downlighting

LK4 4" LED Recessed Kit

IC/Non-IC
New & Remodel Construction



ORDERING INFORMATION


For shortest lead times, configure products using **bolded options**.

Example: LK4BMW LED


| LK4 | B | MW | LED | | |
|--------------------------------|-----------------|-----------------------|-----------------------|----------------------|---------------------|
| Series | Reflector | Finish | Lamps/Lumens | Color Temperature | Voltage |
| LK4 4" LED recessed kit | B Baffle | MW Matte white | LED 400 lumens | (blank) 3000K | (blank) 120V |

Accessories: Order as separate catalog number.

| | |
|-------|--|
| LK4AP | 4" new construction pan |
| LKABH | Hanger bars for conversion to new construction |



LK4AP
New Construction Pan




LKABH
Hanger Bars


4" LED Recessed Downlighting Kit

INSTALLATION


The following instructions are for remodel applications. New construction applications require new construction pan and hanger bars (see accessories).




Step 1:
Using provided stencil, trace cutout lines for housing hole on ceiling. Use saw to make appropriate 4-1/8" cutout.



Step 2:
Using provided wire connectors, connect wires (black to black; white to white; ground to ground) and insert housing into ceiling.



Step 3:
Snap (3) springs to secure housing to ceiling.



Step 4:
Insert trim into housing.

DIMMING & ENERGY DATA

| COMPATIBLE DIMMER SWITCHES | | |
|----------------------------|--------------|-------------|
| MANUFACTURER | MODEL/SERIES | PART NO. |
| LUTRON | Skylark | CTCL-153PDH |
| | | S2-LH-WH |
| | | S-10PR |
| | Diva | DV-600PR |
| | Toggler | TGLV-600PR |
| LEVITON | Decora | IPI06 |
| | | 6631 |
| | | 6683 |
| | Vizia | VPI06 |
| COOPER | Aspire | 9530 |

| ENERGY DATA* | |
|--------------------|------------------------------------|
| Lumens | 400 |
| Min. starting temp | -18°C (0°F) |
| EMI/RFI | FCC Title 47 CFR, Part 15, Class B |
| Sound rating | Class A standards |
| Input voltage | 120V |
| Min. power factor | 0.80 |
| Input frequency | 50/60 Hz |
| Rated wattage | 9.0W |
| Input power | 9.0W |
| Input current | 0.089A |

*Values at non-dimming line voltage.