

Izj0iL3dpcmUtY2FibGUtbWFuYWdlbWVudC9yYWNld2F5cy5hc3B4Ij5SYWNld2F5czwvYT4gPGRpdjBjbGFzcz0iZm91cnRoLWx2bCBjb2wzlj4gPGEgaWQ9Im



designed to be better.

Search

Commercial Occupancy Sensor, White

CSU600

Ultrasonic Ceiling Sensor, Occupancy 500 sq.ft, White

Submit Query

Where to buy


Submit Query

Like 0

Tweet 0

0

Email Print





product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Advanced signal processing circuitry helps to eliminate false ONs.
- Utilizes advanced, omni-directional (360 degrees), Doppler technology for reliable occupancy detection.
- Angled transmitter and receiver pairs help optimize sensitivity while eliminating unwanted detection from ceiling air movement.
- Digital DIP switch time delay (15 seconds to 30 minutes).
- LED indicates occupancy detection.
- Reliable solid-state construction.
- Temperature and humidity resistant 32 kHz receivers.
- Mounts to ceiling tiles or box.
- Units per power pack: up to 4.
- cULus listed.
- 5-year warranty.

Top 5 Resources

- [Commercial Lighting Controls \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)
- [Commercial Ceiling & Wall or Ceiling Mount Occupancy Sensors, SF3501R1 \(Cutsheet\)](#)
- [CSU Series 32 kHz Ultrasonic Occupancy Sensors \(Installation Instructions\)](#)
- [Perfect Sense Sensor \(Brochure\)](#)

specifications

General Info

- Color: White
- Type: Occupancy
- Features: Ultrasonic

Listing Agencies/Third Party Information

- cU Lus: Yes
- U N SPS C: 39121559

Dimensions

- Depth (U S): 1.5"
- Diameter U S: 4.8"

Technical Information

- Amps: 27mA
- Mounting: Ceiling
- Volts: 24VDC

Buy American Act Compliance

- Country of Origin: TAIWAN
- Buy American Act Status: Trade Agreement Act Compliant

resources

BROCHURE

- [Commercial Lighting ControlsPDF \(323.03kb\)](#)
- [Commercial & Industrial ProductsPDF \(3.52mb\)](#)
- [Perfect Sense SensorPDF \(2.83mb\)](#)

CUTSHEET

- [Commercial Ceiling & Wall or Ceiling Mount Occupancy Sensors, SF3501R1PDF \(248.71kb\)](#)

INSTALLATION INSTRUCTIONS

- [CSU Series 32 kHz Ultrasonic Occupancy SensorsPDF \(1.8mb\)](#)