



designed to be better.

[Search](#)

Non-Fusible Mechanical Interlock

PS460MIR7W

Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 60 amp, 3Ø, 480 vac.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Pin & Sleeve Mechanical Interlock IEC 309-1, 309-2 Configuration 20,30,60,100 amp \(Instruction Sheet No.\)](#)

specifications

General Info

- Type: Pin & Sleeve Non-Fusible Mechanical Interlock Receptacle
- Number Of Poles: 3
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Technical Information

- Amps: 60 Amp
- Volts: 3ø 480VAC
- Volts A C: 480

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-




resources

BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

INSTRUCTION SHEET NO.

 Pin & Sleeve Mechanical Interlock IEC 309-1, 309-2 Configuration 20,30,60,100 ampPDF (8.9mb)